

RB14L4



Article Number: 151-00506

RB Adhesive Cable Clamp, .55" Max. Bundle Dia., PA66, Natural, 200/pkg



Download spec sheet

Base Data

Local Order Number RB14L4

Type RB14

Color Natural (NA)

Features and Benefits

- Simple snap in design allows for quick and easy installation or removal of cables.
- Rubber based adhesive allows for a permanent bond to most surfaces.

Product Description The RB Adhesive cable clamps are designed with an easy snap in feature allowing simple installation or removal of cables, pipes or hoses. The rubber based adhesive allows for a permanent bond to most surfaces. Available in three sizes.

Short Description RB Adhesive Cable Clamp, .55" Max. Bundle Dia., PA66, Natural, 200/pkg

Product Dimensions

Length L (Imperial) 1.3 "

Length L (Metric) 33.2 mm

Fixation Method Pasting / Stick

Variant Closed

Width W (Imperial) 1.1 "

Width W (Metric) 27.4 mm

Width W2 (Imperial) 0.9 "

Width W2 (Metric) 23.0 mm

Height H (Imperial) 0.63 "

Height H (Metric) 16.0 mm

Bundle Diameter Max. (Imperial) 0.55 "

Bundle Diameter Max. (Metric) 14.0 mm

Nominal Diameter (Imperial) 1/2 "

Nominal Diameter (Metric) 14 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 200 Pieces

Carton Quantity 200

Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Adhesive Shortcut Synthetic rubber T60

Adhesive Synthetic rubber with base of polyethylene foam

Adhesive Operating Temperature -40°F to +140°F (-40°C to +60°C)

Flammability UL94 V2 (excluding adhesive)

Halogenfree Yes

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes