

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1502010006](#)
Status: **Active**
Overview: [Ditto™ Wire-to-Wire Interconnects](#)
Description: [Ditto™ Genderless Crimp Housing, Positive Lock, 6 Circuit, Glow Wire Capable](#)

Documents:

Drawing (PDF)	Test Summary TS-150170-0000 (PDF)
Product Specification PS-150170-0000 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-150170-0000 (PDF)	

General

Product Family	Crimp Housings
Series	150201
Application	Power, Wire-to-Wire
Overview	Ditto™ Wire-to-Wire Interconnects
Product Name	Ditto™
UPC	889056215770

Physical

Circuits (maximum)	6
Color - Resin	Natural (White)
Gender	Genderless
Glow-Wire Compliant	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.686/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Temperature Range - Operating	-40°C to +105°C, -40°C to +80°C, See Product Specification


Electrical

Current - Maximum per Contact	4.5A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-150170-0000
Product Specification	PS-150170-0000
Sales Drawing	SD-150201-0000
Test Summary	TS-150170-0000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

Search Parts in this Series

[150201](#) Series

Mates With

Ditto™ Genderless Crimp Housing [150201](#)

Use With

Ditto™ Genderless Terminals [150200](#)