


Capacitor, Tantalum, 15 uF, +/-10% Tol, 15 V



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	4.57	MAX
L	8.76	MAX
F	0.51	+/-0.05
LL	38.1	+/-6.35

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	100

General Information	
Supplier:	KEMET
Application:	General Purpose
Body Type:	Axial
Lead Type:	Un-insulated Wire
Termination Type:	Tin (Sn)
RoHS:	Yes

Specifications	
Capacitance:	15 uF
Tolerance:	+/-10%
Voltage:	15 VDC (85C)
Voltage:	12 VDC (125C Surge)
Voltage:	0.15 V (125C Reverse)
Temperature Range:	-55/+125C
Resistance/ESR:	2.5 Ohms (100kHz)
Leakage Current:	1.5 uA
Dissipation Factor:	6%