

PRINTING RIBBONS AND INKS TECHNICAL DATASHEET

TTDS-257 Revision 6, March 2016

Section 1, Contents

SECTION	PAGE	SECTION DESCRIPTION	COLOUR AND TYPE
Section 1	Page 1	CONTENTS	
Section 2	Page 2	1966-RIBBONS, 2000P-4TT, T300-RIBBON-UV-SCE	BLACK THERMAL TRANSFER
Section 3	Page 3	TMS-XXX-RIBBON-XXX	BLACK THERMAL TRANSFER
Section 4	Page 4 & 5	TTB-XXXX/XXX	BLACK THERMAL TRANSFER
Section 5	Page 6 & 7	1330-XXXX-XX	BLACK THERMAL TRANSFER
Section 6	Page 8 & 9	WHITE & SILVER	WHITE & SILVER THERMAL TRANSFER
Section 7	Page 10	BTT-02 CARD PRINTER	BLUE, RED, BLACK AND WHITE THERMAL TRANSFER
Section 8	Page 11	DOT MATRIX	BLACK INK CARTRIDGES

PAGE 1

Section 2, BLACK 1966-RIBBONS, 2000P-4TT, T300-RIBBON-UV-SCE

Ribbon Description	Part number	Shelf life and storage conditions	Length	Width	Core size	Ink side	Colour
1966-RIBBON	F55931-000	3 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	100mm (3.9 inches)	25.4mm (1 inch)	Ink side out	Black
LBF-2000P-RIBBON-1966-MED	6-1768383-4	3 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	60mm (2.36 inches)	25.4mm (1 inch)	Ink side out	Black
T200-RIBBON-1966	D60849-000	3 years, when stored between -5°C (23°F) and 40° (104°F)	74m (242 feet)	110mm (4.3 inches)	12.7mm (1/2 inch)	Ink side out	Black
2000P-RIBBON-4TT-MED	893803-000	3 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	60mm (2.36 inches)	25.4mm (1 inch)	Ink side out	Black
2000P-RIBBON-4TT-NAR	277493-000	3 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	40mm (1.57 inches)	25.4mm (1 inch)	Ink side out	Black
T300-UV-SCE-RIBBON	EC8932-000	1 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	110mm (4.33 inches)	25.4mm (1 inch)	Ink side out	Black

Section 3, BLACK TMS THERMAL TRANSFER RIBBONS

Ribbon Description	Part number	Shelf life and storage conditions	Length	Width	Core size	Ink side	Colour
TMS-RJS-RIBBON-4DSCE	311292-000	2 years, when stored between -5°C (23°F) and 40°C (104°F)	450m (1476 feet)	110mm (4.33 inches)	25.4mm (1 inch)	Ink side out	Black
TMS-101-RIBBON-4DSCE	505478-000	2 years, when stored between -5°C (23°F) and 40°C (104°F)	74m (242 feet)	110mm (4.33 inches)	12.7mm (1/2 inch)	Ink side out	Black
TMS-RJS-RIBBON-4RPSCE	557721-000	3 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	110mm (4.33 inches)	25.4mm (1 inch)	Ink side out	Black
TMS-101-RIBBON-4RPSCE	310109-000	3 years, when stored between -5°C (23°F) and 40°C (104°F)	74m (242 feet)	110mm (4.33 inches)	12.7mm (1/2 inch)	Ink side out	Black
TMS-RJS-RIBBON-4HT	754073-000	3 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	110mm (4.33 inches)	25.4mm (1 inch)	Ink side out	Black
TMS-101-RIBBON-4HT	746617-000	3 years, when stored between -5°C (23°F) and 40°C (104°F)	74m (242 feet)	110mm (4.33 inches)	12.7mm (1/2 inch)	Ink side out	Black

Section 4, BLACK TTB THERMAL TRANSFER RIBBONS

Ribbon Description	Part number	Shelf life and storage conditions	Length	Width	Core size	Ink side	Colour
TTB-060SC/300	2-1768049-6	1 year, when stored between 5 (40°F) and 35°C (95°F)	300m (984 feet)	60mm (2.36 inches)	25.4mm (1 inch)	Ink side in	Black
TTB-076SC/300	3-1768049-0	1 year, when stored between 5 (40°F) and 35°C (95°F)	300m (984 feet)	76mm (3 inches)	25.4mm (1 inch)	Ink side in	Black
TTB-084SC/300	C75514-000	1 year, when stored between 5 (40°F) and 35°C (95°F)	300m (984 feet)	84mm (3.3 inches)	25.4mm (1 inch)	Ink side in	Black
TTB-110SC/300	3-1768049-6	1 year, when stored between 5 (40°F) and 35°C (95°F)	300m (984 feet)	110mm (4.33 inches)	25.4mm (1 inch)	Ink side in	Black
TTB-128SC/450	4-1768049-1	1 year, when stored between 5 (40°F) and 35°C (95°F)	450m (1476 feet)	128mm (5.04 inches)	25.4mm (1 inch)	Ink side out	Black
TTB-170SC/450	4-1768049-7	1 year, when stored between 5 (40°F) and 35°C (95°F)	450m (1476 feet)	170mm (6.70 inches)	25.4mm (1 inch)	Ink side out	Black

Section 4, BLACK TTB THERMAL TRANSFER RIBBONS (Continued)

Ribbon Description	Part number	Shelf life and storage conditions	Length	Width	Core size	Ink side	Colour
TTB-110SC/300WH	3-1768049-8	1 year, when stored between 5 (40°F) and 35°C (95°F)	300m (984 feet)	110mm (4.30 inches)	25.4mm (1 inch)	Ink side in	Black
TTB-060SC/450AQ529	2-1768049-7	1 year, when stored between 5°C (40°F) and 35°C (95°F)	450m (1476 feet)	60mm (2.36 inches)	25.4mm (1 inch)	Ink side in	Black
TTB-090SC/360-AQ529	3-1768049-4	1 year, when stored between 5°C (40°F) and 35°C (95°F)	360m (1181 feet)	90mm (3.54 inches)	25.4mm (1 inch)	Ink side in	Black
TTB-110SC/300AQ529S	3-1768049-7	1 year, when stored between 5°C (40°F) and 35°C (95°F)	300m (984 feet)	110mm (4.33 inches)	25.4mm (1 inch)	Ink side out	Black
TTB-114SC/360AQ529	4-1768049-0	1 year, when stored between 5°C (40°F) and 35°C (95°F)	360m (984 feet)	114mm (4.48 inches)	25.4mm (1 inch)	Ink side out	Black
TTB-166SC/360AQ529	8-1768402-6	1 year, when stored between 5°C (40°F) and 35°C (95°F)	360m (1181 feet)	166mm (6.53 inches)	25.4mm (1 inch)	Ink side out	Black

Section 5, BLACK 1330 THERMAL TRANSFER RIBBONS

Ribbon Description	Part number	Shelf life and storage conditions	Length	Width	Core size	Ink side	Colour
1330-0600-10	143060-000	2 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	110mm (4.33 inches)	25.4mm (1 inch)	Ink side out	Black
1330-0600-T200	C36369-000	2 years, when stored between -5°C (23°F) and 40°C (104°F)	74m (242 feet)	110mm (4.33 inches)	12.7mm (1/2 inch)	Ink side out	Black
1330-TTB-T200	1-1768384-8	1 year, when stored between 5°C (40°F) and 35°C (95°F)	74m (242 feet)	110mm (4.33 inches)	12.7mm (1/2 inch)	Ink side out	Black
1330-3300-15	562492-000	3 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	165mm (6.5 inches)	25.4mm (1 inch)	Ink side out	Black
1330-3300-10	980892-000	3 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	110mm (4.3 inches)	25.4mm (1 inch)	Ink side out	Black
1330-3300-08	728382-000	3 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	80mm (3.15 inches)	25.4mm (1 inch)	Ink side out	Black
1330-3300-06	F31906-000	3 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	64mm (2.52 inches)	25.4mm (1 inch)	Ink side out	Black
1330-3300-101TT	C95590-000	3 years, when stored between -5°C (23°F) and 40°C (104°F)	74m (242 feet)	110mm (4.3 inches)	12.7mm (1/2 inch)	Ink side out	Black

Section 5, BLACK 1330 THERMAL TRANSFER RIBBONS (Continued)

Ribbon Description	Part number	Shelf life and storage conditions	Length	Width	Core size	Ink side	Colour
1330-0607-10	742412-000	2 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	110mm (4.33 inches)	25.4mm (1 inch)	Ink side out	Black
1330-0607-08	555080-000	2 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	80mm (3.15 inches)	25.4mm (1 inch)	Ink side out	Black
1330-0607-T200	E45478-000	2 years, when stored between -5°C (23°F) and 40°C (104°F)	74m (242 feet)	110mm (4.33 inches)	12.7mm (1/2 inch)	Ink side out	Black
1330-0619-10	952888-000	2 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	110mm (4.33 inches)	25.4mm (1 inch)	Ink side out	Black
1330-0619-08	F65920-000	2 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	83mm (3.27 inches)	25.4mm (1 inch)	Ink side out	Black
1330-0619-T200	C49013-000	2 years, when stored between -5°C (23°F) and 40°C (104°F)	74m (242 feet)	110mm (4.33 inches)	12.7mm (1/2 inch)	Ink side out	Black

Section 6, WHITE and SILVER THERMAL TRANSFER RIBBONS

Ribbon Description	Part number	Shelf life and storage conditions	Length	Width	Core size	Ink side	Colour
T300-RIBBON-WH-4HT	154739-000	2 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	110mm (4.33 inches)	25.4mm (1 inch)	Ink side out	White
T200-RIBBON-WH-4HT	086961-000	2 years, when stored between -5°C (23°F) and 40°C (104°F)	74m (242 feet)	110mm (4.33 inches)	12.7mm (1/2 inch)	Ink side out	White
T300-RIBBON-WH	650784-000	2 year, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	110mm (4.33 inches)	25.4mm (1 inch)	Ink side out	White
T200-RIBBON-WH	117366-000	2 year, when stored between -5°C (23°F) and 40°C (104°F)	74m (242 feet)	110mm (4.33 inches)	12.7mm (1/2 inch)	Ink side out	White
2000P-RIBBON-WH-MED	094514-000	2 year, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	60mm (2.36 inches)	25.4mm (1 inch)	Ink side out	White
2000P-RIBBON-WH-NAR	530304-000	2 year, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	40mm (1.57 inches)	25.4mm (1 inch)	Ink side out	White
RIB-1976-076360-0L-9	1-2186321-1	1 years, when stored between -5°C (23°F) and 40°C (104°F)	360m	76mm	25.4mm	Ink side out	White
RIB-1976-110300-0L-9	1-2186043-1	1 years, when stored between -5°C (23°F) and 40°C (104°F)	300m	110mm	25.4mm	Ink side out	White

Section 6, WHITE and SILVER THERMAL TRANSFER RIBBONS (Continued)

Ribbon Description	Part number	Shelf life and storage conditions	Length	Width	Core size	Ink side	Colour
TMS-RJS-RIBBON-4AG	124503-000	5 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	110mm (4.33 inches)	25.4mm (1 inch)	Ink side out	Silver
TMS-101-RIBBON-4AG	252557-000	5 years, when stored between -5°C (23°F) and 40°C (104°F)	74m (242 feet)	110mm (4.33 inches)	12.7mm (1/2 inch)	Ink side out	Silver
2000P-RIBBON-4AG-MED	351013-000	5 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	60mm (2.36 inches)	25.4mm (1 inch)	Ink side out	Silver
2000P-RIBBON-4AG-NAR	346933-000	5 years, when stored between -5°C (23°F) and 40°C (104°F)	300m (984 feet)	40mm (1.57 inches)	25.4mm (1 inch)	Ink side out	Silver

Section 7, BTT-02 CARD PRINTER THERMAL TRANSFER RIBBONS

Ribbon Description	Part number	Shelf life and storage conditions	Length	Width	Core size	Ink side	Colour
BBB-060BL/200	1-1768016-1	2 years, when stored between -5°C (23°F) and 40°C (104°F)	200m (656 feet)	60mm (2.36 inches)	12.7mm (1/2 inch)	Ink side out	Blue
BBB-060RT/200	1-1768016-3	2 years, when stored between -5°C (23°F) and 40°C (104°F)	200m (656 feet)	60mm (2.36 inches)	12.7mm (1/2 inch)	Ink side out	Red
BBB-060SC/200	1-1768016-4	2 years, when stored between -5°C (23°F) and 40°C (104°F)	200m (656 feet)	60mm (2.36 inches)	12.7mm (1/2 inch)	Ink side out	Black
BBB-060WE/200	1-1768016-5	2 years, when stored between -5°C (23°F) and 40°C (104°F)	200m (656 feet)	60mm (2.36 inches)	12.7mm (1/2 inch)	Ink side out	White

Section 8, DOT MATRIX INK CARTRIDGES

Ribbon Description	Part number	Shelf life and storage conditions	Colour
LQ590-RIBBON	1-2186029-1	6 months When stored between 18°C (64°F) and 24°C (75°F) then 90 days after opening the inner packaging. Ink cartridge Obsolete	Black
TMS-SYSTEM-SIX-RIBBON-A	310347-000	6 months When stored between 18°C (64°F) and 24°C (75°F) then 90 days after opening the inner packaging. Ink cartridge Obsolete	Black
TMS-LQ590-RIBBON	CC3130-000	6 months When stored between 18°C (64°F) and 24°C (75°F) then 90 days after opening the inner packaging. Ink cartridge Obsolete	Black
TMS-SYSTEM-SIX-RIBBON-B	264327-000	6 months When stored between 18°C (64°F) and 24°C (75°F) then 90 days after opening the inner packaging. Ink cartridge Obsolete	Black
1892BK04-RIBBON	D06106-000	6 months When stored between 18°C (64°F) and 24°C (75°F) then 90 days after opening the inner packaging. Ink cartridge Obsolete	Black
1892BK03-HIGH-PERF-RIBBON	A72722-000	6 months When stored between 18°C (64°F) and 24°C (75°F) then 90 days after opening the inner packaging. Ink cartridge Obsolete	Black
18910000-OKI380-RIBBON	856832-000	6 months When stored between 18°C (64°F) and 24°C (75°F) then 90 days after opening the inner packaging. Ink cartridge Obsolete	Black
1330-0037-00	9-1198202-3	6 months When stored between 18°C (64°F) and 24°C (75°F) then 90 days after opening the inner packaging. Ink cartridge Obsolete	Black

Printer Information

Print quality and print performance can only be guaranteed when specific TE printer and ribbons are used.

The current list of printers and ribbons can be found in TE document 411-121005 'Identification Printer Product Ribbon Matrix'. This document can be found in 'Access Our Tools':

<http://www.te.com/usa-en/utilities/access-product-tools-and-resources.html>

Software

WINTOTAL and PrintEasy label printing software, available from the Identification Printer Software page:

<http://www.te.com/usa-en/products/identification-labeling/printers-software/printing-software.html?tab=pgp-story>

Contact a TE representative for further information

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2014 TE Connectivity Ltd. family of companies All Rights Reserved.