

MSMP5-109C2

Article Number: 151-25519

Mounting Plate, 8.05" Length, .62" Width, .2" Hole Dia., .3" Max. Tie Width, PA66, Natural, 100/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number MSMP5-109C2

Type MSMP5/10

Color Natural (NA)

Features and Benefits

- Mounting plates allow multiple bundles to run parallel.
- The mounts are secured using two screws, while the bundles are attached using cable ties in any of the available slots.

Product Description HellermannTyton mounting plates allow multiple cable to be run in parallel. The mount is secured with two screws and the cables are attached to the plate by using a cable tie through any of the available slots.

Short Description Mounting Plate, 8.05" Length, .62" Width, .2" Hole Dia., .3" Max. Tie Width, PA66, Natural, 100/pkg

Product Dimensions

Length L (Imperial) 8.05 "

Length L (Metric) 204.5 mm

Fixation Method Screw Mounting and Rivet

Number of Bundles 5

Width W (Imperial) 0.62 "

Width W (Metric) 15.8 mm

Cable Tie Width Max. (Imperial) 0.3 "

Cable Tie Width Max. (Metric) 7.6 mm

Height H (Imperial) 0.21 "

Height H (Metric) 5.3 mm

Mounting Hole Diameter D (Imperial) 0.2 "

Mounting Hole Diameter D (Metric) 5.1 mm

Mounting Hole Centers (Imperial) 1.5 "

Mounting Hole Diameter D Max. (Metric) 5.1 mm

Mounting Hole Diameter D Min. (Metric) 5.1 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100 Pieces

Carton Quantity 1 Pieces

Weight (Metric) 1.9 kg

Material and Specifications

Material Polyamide 6.6 (PA66)
Material Shortcut PA66
Flammability UL94 V2
Operating Temperature -40°F to +185°F (-40°C to +85°C)
ROHS Compliant Yes
Certification/Specification UL
UL Listed (US and Canada) No
UL Recognized (US and Canada) Yes