


**PRODUCT
DATA SHEET**

Type	Size	Rating	Description	Part No.
Incandescent	T5	12V 2W	T-1½ Wedgebase Lamp	924-002LF



PHOTOMETRY DATA

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE (Hours)
	Min.	Nom.	Max.	Min.	Nom.	Max.	
12.0	148	165	182	6.0	7.5	9.0	1000

NOTES:

- 1) W2x4.6d in accordance with IEC 61-1, (BS EN 60061-1), sheet 7004-94-x.
- 2) C-2V filament shape.
- 3) Clear Glass bead.
- 4) Lamp components are lead-free
- 5) Lamp marking: VCH . X
12V2W Y to be durably printed on the bulb, where X & Y are a lot code.

Issue No.	Date	C.N. No.	Drawn	Tech	QA	Sales
2	22/11/06	-	BCW	Approved		