

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0501258000**  
**Status:** **Active**  
**Overview:** PicoBlade™ Connector System  
**Description:** 1.25mm Pitch PicoBlade™ Crimp Terminal 50125, 26-28 AWG, Reel

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-51021-009 \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<u>50125</u>
Application	Signal
Crimp Quality Equipment	Yes
Current Derating Order No	987651-3691
Overview	<u>PicoBlade™ Connector System</u>
Product Name	PicoBlade™
UPC	800753630260

**Physical**

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	17.100/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.50-1.00mm
Wire Size AWG	26, 28
Wire Size mm²	N/A


**Electrical**

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

**Material Info**

**Reference - Drawing Numbers**

Crimp Specification	CS-50125_50133
Product Specification	PS-51021-009, RPS-50125-001, RPS-51021-033
Sales Drawing	SD-50125-8*00



**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per  
-ED/79/2015 (17  
December 2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Compliant

**Search Parts in this Series**

50125 Series

**Mates With**

50058 Crimp Terminal, 50079 Crimp Terminal

**Use With**

51047 Crimp Housing

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

FineAdjust™  
Applicator for  
1.25mm Pitch Board

0639004200

In, Wire-to-Board  
and Wire-to-Wire  
Terminal, 26-32  
AWG  
T2 Terminator 0639104200  
Tooling Die  
Extraction Tool 0011030043  
Hand Crimp Tool for 0638190400  
1.25mm Pitch Crimp  
Terminals, 26-32  
AWG Wire

**Japan**  
**Description** **Product #**

Extraction Tool 0570726000  
Applicator for M21 1A 0571383000  
Bench Press, 26-32  
AWG Wire  
Side-Feed Applicator 0571383200  
For Full-Auto  
Machine

This document was generated on 03/31/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**