

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191990008**
Status: **Active**
Overview: [Splices](#)
Description: Avikrimp™ Window Butt Connector for 18-22 AWG Wire, Mylar Tape Carrier

Documents:

Drawing (PDF)	Product Specification PS-19902-015 (PDF)
Product Specification PS-19902-011 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Splices
Series	19199
Comments	Mil Spec M7928/5-3
Crimp Quality Equipment	Yes
Mil-Spec	M7928/5-3
Overview	Splices
Product Name	Avikrimp™, Butt - Window
UPC	800753046818

Physical

Barrel Type	Closed
Color - Resin	Red
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.194/g
Packaging Type	Adhesive Tape on Reel
Temperature Range - Operating	-55°C to +105°C
Wire Insulation Diameter	3.56mm max.
Wire Size AWG	18, 20, 22
Wire Size mm²	0.25-1.50

Electrical

Voltage - Maximum	300V
-------------------	------

Material Info

Old Part Number	WA-840T
-----------------	---------

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-015
Sales Drawing	SD-19199-003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Not Relevant
ELV	Not Relevant

Search Parts in this Series

19199 Series

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	0192880043
Mini-Mac™ Applicator Air Feed- Mylar Tape	0638859100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION