

General

Size (Inch)	23.5" / 59.8cm
Panel Type	TN
Color Gamut (CIE1976)	72%
Colour Depth (Num of Colours)	16.7M colors
Pixel Pitch (mm)	0.2715 x 0.2715
Aspect Ratio	16:9
Resolution	1920 x 1080
Brightness(Typ.)	200cd/m ²
Contrast Ration (DFC)	5M:1
Response Time_Typ.(on/off)	5ms
Viewing Angle(CR≥10)	170/160
Surface Treatment	Anti-Glare,3H

Jack Input / Output

D-Sub	Yes
HDMI	Yes
[Jack Location]	Back
Headphone Out	Yes
Jack Location(Audio Output)	Back

Power

Type	Adapter
Input	100-240Vac, 50/60Hz
Consumption(Normal On(EPA))	19W
Normal On(typ.)	25W
Sleep Mode(Max)	0.3W
DC Off(Max)	0.3W

Frequency

D-sub(H-Frequency)	30~83kHz
D-sub(V-Frequency)	56~75Hz
HDMI(H-Frequency)	30~83kHz
HDMI(V-Frequency)	56~75Hz

Resolution

PC(D-sub)	1920X1080
Digital (DVI-D / HDMI)	1920X1080

Control Key

Key Number (Power Key Included)	6
Key Type	Tact Type
LED Color(On mode)	White
LED Color(Power save mode)	White Blinking
[Key Location]	Bottom

OSD

Language(Country)	English, Germanic, French, Spanish, Italian, Swedish, Finnish, Portuguese, Polish, Russian, Greek, Chinese, Japanese, Korean, Ukrainian, Portuguese(Brazil), Hindi
Number of Language	17

Special Feature

Picture Mode	Yes
--------------	-----

Reader Mode	Yes
Original Ratio	Yes
DDC/CI	Yes
HDCP	Yes
Intelligent Auto (Auto Adjustment)	Yes
Key Lock	Yes
Plug & Play	Yes
Color weakness	Yes
Flicker Safe	Yes
Automatic standby	Yes
Smart Energy saving	Yes
4 screen split	Yes
OnScreen Control	Yes
Others	Yes

Color

Front	Black Hairline
B/Cover	Black Texture
Stand	Black high glossy
Base	Black Hairline

Stand

Base detachable	Yes
Tilt(Angle)	Yes: -5° ~ 20°

Dimensions - WxDxH (mm)

Set (with Stand)	556.2 x186.7 x415.1
Set (without Stand)	556.2 x 56.8 x 344.0

Box	624x409x124
Wall Mount size (mm)	100x100

Weight(Kg)

Set (with Stand)	2.8
Set (without Stand)	2.6
Box	4.1

Stuffing

Pallet(20ft/40ft/40ft HC)	680/1496/1672
---------------------------	---------------

Wrap

Packing Material	EPS
Stacking Type	Face Down
Box Printing Type	Flexo
Handle	Handle

Standard

UL (cUL)	Yes
TUV-Type	Yes
FCC-B, CE	Yes
EPA 6.0	Yes
Erp	Yes
Windows	Yes(win 10)
