

General

Size (Inch)	21.5"
Panel Type	IPS
Color Gamut (CIE1976)	72%
Colour Depth (Num of Colours)	16.7M colors
Pixel Pitch (mm)	0.24795x0.24795
Aspect Ratio	16:9
Resolution	1920 x 1080
Brightness(Typ.)	250cd/m2
Contrast Ratio(Original)	1000:1
(DFC)	Mega
(GTG)	5ms
Viewing Angle(CR≥10)	178/178
Surface Treatment	Anti-Glare,3H

Jack Input / Output

D-Sub	Yes
DVI-D	Yes
HDMI	Yes
[Jack Location]	Back (horizontal)

Audio Output

Headphone Out	Yes
[Jack Location]	Back

Power

Input/Output (Type)	Adapter
Input	100-240Vac, 50/60Hz
Output	19V/1.3A
Consumption(Normal On(EPA))	20W
Normal On(typ.)	24W
Sleep Mode(Max)	0.3W
DC Off(Max)	0.3W

Frequency

D-sub H-Frequency	30~83kHz
D-sub V-Frequency	56~75Hz
DVI-D H-Frequency	30~83kHz
DVI-D V-Frequency	56~75Hz
HDMI H-Frequency	30~83kHz
HDMI V-Frequency	56 ~ 75Hz

Resolution

PC D-sub	1920X1080
Digital (DVI-D / HDMI)	1920X1080
Video HDMI	1080P

Control Key

Key Number (Power Key Included)	1
Key Type	Joystick
LED Color(On mode)	White
LED Color(Power save mode)	White Blinking
[Key Location]	Bottom

OSD

Language/Country	English, Germanic, French, Spanish, Italian, Swedish, Finnish, Portuguese, Polish, Russian, Greek, Chinese, Japanese, Korean, Ukrainian, Portuguese(Brazil), Hindi
Number of Language	17

Special Feature

Picture Mode	Custom, Reader 1, Reader 2, Photo, Cinema, Game, Color Weakness
Reader Mode	Yes
Original Ratio	Yes
DDC/CI	Yes
HDCP	Yes
Intelligent Auto (Auto Adjustment)	Yes
Key Lock	Yes
Plug & Play	Yes
Response Time Control	Yes
Color weakness	Yes
Flicker Safe	Yes
Automatic standby	Yes
Six Axis Control	Yes
Smart Energy saving	Yes
Super Resolution+	Yes
4 screen split	Yes
OnScreen Control	Yes
Black Stabilizer	Yes

Color

Front	Black
B/Cover	Black

Stand	Black
Base	Black
Others	Black

Stand

Base Detachable	Yes
Tilt(Angle)	Yes / -2° ~ 15°

Dimension (W*D*H, mm)

Set (with Stand)	510.1*186.8*395.3
Set (without Stand)	510.1*86.8*308.4
Box	578*375*129

Weight (Kg)

Set (with Stand)	2.9kg
Set (without Stand)	2.5kg
Box	3.4kg

Stuffing

Pallet(20ft/40ft/40ft HC)	960/1920/2160
---------------------------	---------------

Wrap

Packing Material	EPS
Stacking Type	Face Down
Stand Packing Type	None

Box Printing Type

Flexo

Handle

Hand Hole

Standard

UL (cUL)

Yes

TUV-Type

Yes

FCC-B, CE

Yes

EPA 6.0

Yes

Erp

Yes

Windows

Win10

Accessory

Power Cord

Option

D-Sub

Option

DVI-D

Option

HDMI

Option

Stand body

Yes

Stand base

Yes

cable holder

Yes

CD

Yes

ESG

Yes

Manual

Yes

ECO

[More Compliance Information](#)
