

General

Size (Inch)	23.8
Panel Type	IPS
Color Gamut (CIE1976)	72%
Color Depth(Number of Colors)	16.7M colors
Pixel Pitch(mm)	0.2745x0.2745
Aspect Ratio	16:9
Resolution	1920 x 1080
Brightness(Typ.)	250cd/m ²
Contrast Ratio(Original)	1000:1
(DFC)	Mega
(GTG)	5ms
Viewing Angle(CR≥10)	178/178
Surface Treatment	Anti-Glare,3H

Jack Input / Output

D-Sub	Yes
DVI-D	Yes
HDMI	Yes
[Jack Location]	Back (horizontal)
Headphone Out	Yes

Power

Input/Output (Type)	Adapter
Input	100-240Vac, 50/60Hz
Output	19V/1.3A
Consumption(Normal On(EPA))	23W
Normal On(typ.)	26W

Sleep Mode(Max)	0.3W
DC Off(Max)	0.3W

Frequency

D-sub(H-Frequency)	30~83kHz
D-sub(V-Frequency)	56~75Hz
DVI-D(H-Frequency)	30~83kHz
DVI-D(V-Frequency)	56~75Hz
HDMI(H-Frequency)	30~83kHz
HDMI(V-Frequency)	56~75Hz

Resolution

PC(D-sub)	1920X1080
Digital (DVI-D / HDMI)	1920X1080
Video(HDMI)	1080P

Control Key

Key Number (Power Key Included)	1
Key Type	Joystick
LED Color(On mode)	White
LED Color(Power save mode)	White Blinking
[Key Location]	Bottom

OSD

Language(Country)	English, Germanic, French, Spanish, Italian, Swedish, Finnish, Portuguese, Polish, Russian, Greek, Chinese, Japanese, Korean, Ukrainian, Portuguese(Brazil), Hindi
-------------------	--

Special Features

Picture Mode	"Custom, Reader 1, Reader 2, Photo, Cinema, Game, Color Weakness"
Reader Mode	Yes (included in Picture Mode)
Original Ratio	Yes
DDC/CI	Yes
HDCP	Yes
Intelligent Auto (Auto Adjustment)	Yes
Key Lock	Yes
Plug & Play	Yes
Response Time Control	Yes
Color weakness	Yes
Flicker safe	Yes
Automatic Standby	Yes
Six Axis Control	Yes
Smart Energy saving	Yes
Super Resolution+	Yes
4 screen split	Yes
OnScreen Control (OSC)	Yes
Others	Black Stabilizer

Color

Front	Black
B/Cover	Black
Stand	Black
Base	Black
Others	Black

Stand

Base detachable	Yes
Tilt(Angle)	Yes / -2° ~ 15°

Dimension(W*D*H)(cm)

Set (with Stand)	550.5*186.8*419
Set (without Stand)	550.5*85.5*332.1
Box	619*395*129

Weight (Kg)

Set (with Stand)	3.2kg
Set (without Stand)	2.8kg
Box	4.3kg

Stuffing

Individual(20ft/40ft/40ft HC)	810/1710/1805
Pallet(20ft/40ft/40ft HC)	720/1600/1800

Wrap

Packing Material	EPS
Stacking Type	Face Down
Box Printing Type	Flexo
Handle	Hand Hole

Standard

UL (cUL)	Yes
TUV-Type	Yes
FCC-B, CE	Yes
EPA 6.0	Yes
Erp	Yes
Windows	Win10

Accessory

Power Cord	Option
D-Sub	Option
DVI-D	Option
HDMI	Option
Cable holder	Yes
Stand body	Yes
Stand base	Yes
CD	Yes
ESG	Yes
Manual	Yes

ECO

[More Compliance Information](#)
