


Game Mode



Fully Geared UP with Winning Features

Black Stabilizer is especially useful to detect objects including enemies that are hiding in dark areas. Dynamic Action Sync allows you to attack enemies faster with less lag time.

Black Stabilizer






Dynamic Action Sync



Black Stabilizer & Dynamic Action Sync **ON**



Up-scaled Work Efficiency



Exceptional Usability

OnScreen Control and My Display Presets allow you to easily customize monitor settings with a few clicks of a mouse

[See Video](#)

General

| | |
|-------------------------------|----------------------|
| Size (Inch) | 25" Flat |
| Panel Type | IPS |
| Color Gamut (CIE1931) | sRGB over 99% |
| Color Depth(Number of Colors) | 8bits, 16.7M |
| Pixel Pitch(mm) | 0.2286mm x 0.2286mm |
| Resolution | 2560 x 1080 |
| Brightness(Typ.) | 250cd/m ² |
| Contrast Ratio(Original) | 1000:1 |
| (DFC) | Mega |
| Response Time_Typ.(on/off) | 14ms |
| (GTG) | 5ms |
| Viewing Angle(CR≥10) | 178/178 |

Jack Input / Output

| | |
|---------------|-------------------|
| HDMI | Yes (ver1.4, 2ea) |
| Headphone Out | Yes |

Power

| | |
|----------------------------|------------|
| Type | Adapter |
| Input | 100 ~ 240V |
| Normal On(EPA6.0) | 24W |
| Normal On(typ.) | 27W |
| Power Save/Sleep Mode(Max) | 0.3W |
| DC Off(Max) | 0.3W |

Frequency

| | |
|-------------------|------------|
| HDMI(H-Frequency) | 30 ~ 90KHz |
| HDMI(V-Frequency) | 56~75Hz |

Special Features

| | |
|----------------------------|---|
| Picture Mode | Custom, Reader1, Reader2, Photo, Cinema, Color Weakness |
| Ratio | Wide, Original |
| PIP | - (PIP mode in Screen Split) |
| DDC/CI | Yes |
| HDCP | Yes |
| Key Lock | Yes |
| Response Time Control | Yes |
| Game Mode | Yes |
| DAS Mode | Yes |
| Black Stabilizer | Yes |
| Flicker Safe | Yes |
| Smart Energy saving | Yes |
| Automatic standby | Yes |
| Reader Mode | Yes (Picture Mode) |
| Six Axis Control | Yes |
| Dual controller | Yes |
| Screen split2.0 (in OSC) | Yes |
| My Display Preset (in OSC) | Yes |
| OnScreen Control (OSC) | Yes |

Stand

| | |
|-------------|--------------|
| Tilt(Angle) | -5~20 Degree |
|-------------|--------------|

Dimensions - WxDxH (mm)

| | |
|---------------------|-----------------|
| Set (with Stand) | 609 x 188 x 383 |
| Set (without Stand) | 609 x 55 x 287 |
| Box | 682 x 355 x 131 |

Weight (Kg)

| | |
|---------------------|-----|
| Set (with Stand) | 4.0 |
| Set (without Stand) | 3.7 |
| Box | 5.4 |

Wall Mount

| | |
|----------------------|---------------------------|
| Wall Mount size (mm) | 75 x 75 (VESA compatible) |
|----------------------|---------------------------|

Wrap

| | |
|--------------------|-----------------|
| Packing Material | EPS |
| Stacking Type | Face Down |
| Stand Packing Type | Base Detach |
| Box Printing Type | Flexo (1 Color) |
| Handle | Handle |

Standard

| | |
|-----------------|-----|
| TCO 6.0 | Yes |
| UL (cUL) | Yes |
| TUV-Type | Yes |
| FCC-B, CE | Yes |
| CCC (for China) | Yes |

| | |
|---------|-----|
| EPA 6.0 | Yes |
| Erp | Yes |
| Windows | Yes |

Accessory

| | |
|------------|-----|
| Power Cord | Yes |
| HDMI | Yes |

ECO

[More Compliance Information](#)

WHAT PEOPLE ARE SAYING

[USER REVIEWS](#)

BE THE FIRST TO WRITE A REVIEW

[WRITE YOUR OWN REVIEW](#)
