

Normal On(EPA6.0)	31W
Normal On(typ.)	56.5W
Power Save/Sleep Mode(Max)	0.5W
DC Off(Max)	0.3W

Frequency

HDMI H-Frequency	30 ~ 90KHz
HDMI V-Frequency	56 ~ 75Hz
Display Port H-Frequency	30 ~ 90KHz
Display Port V-Frequency	56 ~ 75Hz (FreeSync 40~75Hz)

Special Feature

Picture Mode	"Custom, Reader, Photo, Cinema, Color Weakness, FPS Game 1, FPS Game 2, RTS Game, Custom (Game)"
Ratio	Wide, Original, Cinema 1, Cinema 2, 1 : 1
PIP	- (PIP mode in Screen Split)
PBP	Yes
DDC/CI	Yes
HDCP	Yes
Key Lock	Yes
Response Time Control	Yes
Freesync	Yes (DP 40~75Hz)
Game Mode	Yes
DAS Mode	Yes
Black Stabilizer	Yes
Flicker Safe	Yes
Smart Energy saving	Yes
Automatic standby	Yes
Reader Mode	Yes (Picture Mode)
Six Axis Control	Yes

Color Calibrated	Yes
Dual controller	Yes
Screen split2.0 (in OSC)	Yes
My Display Preset (in OSC)	Yes
OnScreen Control (OSC)	Yes
Dual EDID (H/W)	Yes

Mechanic

Stand	Tilt(Angle) : -5~20 Degree
Dimension	Set (with Stand) : 702.5 x 204.7 x 414.0 ; Set (without Stand) : 702.5 x 63.8 x 328.4 ; Box : 780 x 143 x 412
Weight (Kg)	Set (with Stand) : 5.4 ; Set (without Stand) : 4.8 ; Box : 7.5
Wall Mount size (mm)	75 x 75 (VESA compatible)

Wrap

Packing Material	EPS
Stacking Type	Vertical
Stand Packing Type	Base Detach
Box Printing Type	Flexo (1 Color)
Handle	Hand Hole

Standard

TCO 6.0	Yes
UL (cUL)	Yes
TUV-Type	Yes
FCC-B, CE	Yes
CCC (for China)	Yes
EPA 6.0	Yes
Erp	Yes

Windows	Yes
DisplayPort	Yes

Accessory

Power Cord	Yes
HDMI	Yes
Cable holder	Yes

ECO

[More Compliance Information](#)

WHAT PEOPLE ARE SAYING

[USER REVIEWS](#)

BE THE FIRST TO WRITE A REVIEW

[WRITE YOUR OWN REVIEW](#)
