

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008560124](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® Trifurcon™ Crimp Terminal 7258, 22-26 AWG, Bag, Phosphor Bronze Gold \(Au\)](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-40-02 \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
 Series [7258](#)
 Application [Power](#)
 Crimp Quality Equipment [Yes](#)
 Overview [KK® Interconnect System - Molex](#)
 Packaging Alternative [08-56-0123 \(Reel\)](#)
 Product Name [KK®, Trifurcon™](#)
 UPC [800754226677](#)

Physical

Gender [Female](#)
 Material - Metal [Phosphor Bronze](#)
 Material - Plating Mating [Gold](#)
 Material - Plating Termination [Nickel](#)
 Net Weight [0.159/g](#)
 Packaging Type [Bag](#)
 Plating min - Mating [0.762µm](#)
 Plating min - Termination [1.270µm](#)
 Termination Interface: Style [Crimp or Compression](#)
 Wire Insulation Diameter [1.65mm max.](#)
 Wire Size AWG [22, 24, 26](#)
 Wire Size mm² [N/A](#)

Solder Process Data

Lead-freeProcess Capability [N/A](#)

Material Info

Old Part Number [7258-A\(P558\)L](#)

Reference - Drawing Numbers

Product Specification [PS-40-02](#)
 Sales Drawing [SD-7258](#)



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
 ELV

Green Image
 Not Relevant

Search Parts in this Series

[7258 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	0011030016
Hand Crimp Tool for Crimp Terminals	0638117400