

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0190340005**  
**Status:** **Active**  
**Overview:** Snap Plugs and Receptacles  
**Description:** InsulKrimp™ Snap Plug, for 18-22 AWG Wire, 22.61mm Length

**Documents:**

[3D Model](#)  
[Drawing \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#)  
[Product Specification PS-19902-013 \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E152602

**General**

Product Family Quick Disconnects  
 Series 19034  
 Crimp Quality Equipment Yes  
 Insulated Partial  
 MolexKits Yes  
 Overview Snap Plugs and Receptacles  
 Product Name InsulKrimp™  
 Type Snap Plug  
 UPC 800753047327

**Physical**

Barrel Type Closed  
 Flammability 94V-0  
 Gender Male  
 Glow-Wire Compliant No  
 Insulation PVC  
 Lock to Mating Part None  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 1.158/g  
 Orientation Straight  
 Packaging Type Bag  
 Tab Thickness N/A  
 Tab Width N/A  
 Wire Insulation Diameter 3.60mm max.  
 Wire Size AWG 18, 20, 22

**Electrical**


Voltage - Maximum 600V

**Material Info**

Old Part Number A-269X

**Reference - Drawing Numbers**

Product Specification PS-19902-011, PS-19902-013  
 Sales Drawing SD-19034-004



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/108/2014 (17 Dec  
 2014)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

19034 Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are  
 found by selecting the products below.  
 Crimp Height Specifications are then  
 contained in the Application Tooling  
 Specification document.*

**Global**

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	<u>0640050300</u>
PremiumGrade™ Hand Crimp Tool	<u>0640010100</u>
Hand Crimp Tool	<u>0640010300</u>
Hand Crimp Tool	<u>0640050100</u>
Crimp Head for the AT-200™ Pneumatic Hand Tool	<u>0640050100</u>

This document was generated on 03/07/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**