

C221K

21.5" LED Professional CCTV Monitor with Full HD

edgeio

APPLICATION SPECIFIC

The new C221K offers a 21.5" screen capable of Full High Definition quality enhanced by an advanced 3D Digital Comb filter. The multiple interfaces, including BNC In/Out, HDMI, CVBS and VGA enables output from a variety of sources. Wall/stand mounting is easy with VESA 100mm compatibility although an optional height adjustable stand is available. A sheet metal rear cabinet ensures the C221K is built for the tough environment of top level security monitoring. *Please note that the stand (ref: KTHA-1) and wall mount bracket (ref: KTWM-1) are sold separately.*



Monitor Cosmetics:	Black bezel with black metal rear cabinet
LCD/LED:	21.5" (54.7 cm) LED backlight active matrix, TFT
Pixel Pitch (mm):	0.248mm
Native Resolution:	1920 x 1080 Full HD
Scan Frequency:	Horizontal: 30kHz - 80kHz Vertical: 60Hz - 75Hz
View Angle	CR ≥ 5: Horizontal: 178° Vertical: 170° CR ≥ 10: Horizontal: 170° Vertical: 160°
Display Area (mm):	476.64 (H) x 268.11 (V)
Display Colour:	16.7 Million
Contrast Ratio Standard:	1000:1
Brightness:	250cd/m2
Response Time:	5ms
Speakers:	2 x 2 Watts integrated
Anti-theft Security:	Kensington® Lock
Compatibility:	Windows, Mac OS
Input Video Signal:	HDMI (Supports: 1080p, 1080i, 720p, 576p, 576i, 480p, 480i) Composite Video BNC In/Out CVBS <i>(Input cables are not supplied)</i>
Input Power Source:	AC 100 - 240V, 50 - 60Hz
Power Management (EPA Compliant):	Normal operation: <41W Stand-by mode: <1W
Operation Environment:	Temperature: 5 - 40°C, Humidity: 10% - 85%
Stand or wall mount bracket:	Stand (ref: KTHA-1) and wall mount bracket (ref: KTWM-1) are SOLD SEPERATELY
Weight:	Net: 5.46kg Gross: 6.67kg
Dimensions (W x D x H):	530mm x 41mm x 321mm
VESA Wall Mount Compliant:	100mm x 100mm
Warranty:	Two years (UK mainland only)
EAN Code:	471 2302921360
Pallet Qty:	70 pcs

