

Choose one component from each of the colored sections to assemble a complete switch.
For other options or further information please contact EAO Switch directly.

Product Profile

The Series 03 is a high quality switch range that includes pushbuttons, indicators, mushroom headed switches and key switches.

Options include self cleaning snap-action switching elements.

Technical drawings see page 9

- IP40 or IP65 Protection (with cover)
- Switch Rating, 10A, 380VAC
- Mounting into 21.2 x 41.2mm cut out
- Illumination using T-6.8 Lamps or LED's
- The standard lenses are available in many different versions, transparent, opaque or translucent
- Screw terminal or plug-in connections

Indicator



Indicator body single with two independent lamp bases, raised, rectangular, black plastic, screw terminals, without bezel

Part No.
03-021.001

For complete switch also order **A**

Illuminated pushbutton



Illuminated single pushbutton actuator, raised, rectangular, black plastic, screw terminals, without bezel

Part No.	Action	Contact type
03-616.011	Momentary	1 pole, form C
03-617.011	Momentary	2 pole, form C
03-618.011	Maintained	1 pole, form C
03-619.011	Maintained	2 pole, form C
03-620.011	Momentary/Maintained	2 pole, form C

For complete switch also order **A**

Illuminated pushbutton



Illuminated double pushbutton actuator with independent contacts, raised, rectangular, black plastic, screw terminals, without bezel

Part No.	Action	Contact type
03-624.011	Momentary	2 pole, form C
03-625.011	Maintained	2 pole, form C
03-626.011	Momentary/Maintained	2 pole, form C
03-627.011	Momentary/Indicator	1 pole, form C
03-628.011	Maintained/Indicator	1 pole, form C

For complete switch also order **A**

Buzzer



Buzzer, plastic bezel, raised, rectangular, 10-50VAC/10-75VDC, screw terminals, 85dB ± 10 at a distance of 0.1m, without bezel

Part No.	Action	Contact type
03-630.011	Momentary/Blocking	2 pole, form C
03-631.011	Maintained/Block release	2 pole, form C
03-632.011	Momentary/Maintained	2 pole, form C

For complete switch also order **A**

Choose one component from each of the colored sections to assemble a complete switch.
For other options or further information please contact EAO Switch directly.



LED



LED, T-6.8, single chip, 12 Volt and 28 Volt.
Also available in 6 Volt, 24 Volt and 48 Volt

Color	Part No.	Voltage
Red	10-2K09.1072	12VAC/DC, 9/17mA
Yellow	10-2K09.1074	12VAC/DC, 9/17mA
Green	10-2K09.1075	12VAC/DC, 4/7mA
Blue	10-2K09.1076	12VAC/DC, 9/17mA
White	10-2K09.1079	12VAC/DC, 9/17mA
Red	10-2K13.1072	28VAC/DC, 9/17mA
Yellow	10-2K13.1074	28VAC/DC, 9/17mA
Green	10-2K13.1075	28VAC/DC, 4/7mA
Blue	10-2K13.1076	28VAC/DC, 9/17mA
White	10-2K13.1079	28VAC/DC, 9/17mA

A Accessories



Lens, translucent or opaque/ribbed, one color for single indicator and pushbutton bodies

Color	Part No.	Lens
Red	03-901.2	Translucent
Yellow	03-901.4	Translucent
Green	03-901.5	Translucent
Blue	03-901.6	Translucent
White	03-901.9	Opaque/ribbed
Black	03-901.0	Opaque/ribbed



Lens, translucent/ribbed, two colors for single indicator and pushbutton bodies

Color	Part No.
Red/Green	03-902.2/5
Red/Red	03-902.2/2
White/White	03-902.9/9

Other color options available, please inquire

A Accessories



Lens, translucent or opaque/ribbed, halved for double pushbutton bodies

Color	Part No.	Lens
Red	03-921.2	Translucent
Yellow	03-921.4	Translucent
Green	03-921.5	Translucent
Blue	03-921.6	Translucent
White	03-921.9	Opaque/ribbed
Black	03-921.0	Opaque/ribbed




Lens, translucent or opaque/ribbed, halved for mechanically interlocked double pushbutton bodies

Color	Part No.	Lens
Red	03-923.2	Translucent
Yellow	03-923.4	Translucent
Green	03-923.5	Translucent
Blue	03-923.6	Translucent
White	03-923.9	Opaque/ribbed
Black	03-923.0	Opaque/ribbed



Front bezel flat and raised, black plastic

Image	Part No.	Product description
1	03-965.0	Front bezel flat
2	03-967.0	Front bezel raised



Choose one component from each of the colored sections to assemble a complete switch.
For other options or further information please contact EAO Switch directly.

A Accessories



Sprayproof cover for IP65 sealing and flap guard for pushbutton switch



Blanking plate




Lens remover for flat bezel, lens remover for raised bezel and LED and lamp remover

Image	Part No.	Product description	Part No.	Image	Part No.	Product description
1	03-924	Sprayproof cover	03-949.0	1	02-905	Lens remover for flat/2 sided bezel
2	03-925	Flap guard		2	98-968	Lens remover for raised/4 sided bezel
				3	51-996	LED remover
				4	02-906	Lamp remover raised/4 sided




03 Indicator

Single




03 Pushbutton

Illuminated, Raised, Single




03 Pushbutton

Illuminated, Raised, Double



03 Buzzer

Raised



03 Cut-outs, Raised Mounting

