

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0500128000**
Status: **Active**
Description: 2.00mm Pitch Crimp Terminal, Reel, for 51006 Housing

Documents:

[3D Model](#) [Packaging Specification SPK-50012-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-51005-001 \(PDF\)](#)

General

Product Family Crimp Terminals
Series [50012](#)
Application Signal
Crimp Quality Equipment Yes
Packaging Alternative [50012-8100](#) (Loose)
Product Name N/A
UPC 800753576230

Physical

Gender Male
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 80.000/mg
Packaging Type Reel
Plating min - Mating 0.889µm
Plating min - Termination 0.914µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 0.90-1.15mm
Wire Size AWG 24, 26, 28
Wire Size mm² N/A


Electrical

Current - Maximum per Contact 2.0A
Voltage - Maximum 125V

Material Info

Reference - Drawing Numbers

Crimp Specification [CS-50012_50013](#)
Packaging Specification [SPK-50012-001](#)
Product Specification [PS-51005-001](#)
Sales Drawing [SD-50012-001](#)



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[50012](#) Series

Mates With

[50013](#)

Use With

[51006](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

FineAdjust™ [0638615000](#)
Applicator
Hand Crimp Tool, UL [0638117800](#)
Approved

T2 Terminator Die 0638515000

Japan

Description **Product #**

Applicator for M211A 0570453000

Bench Press, 24-28

AWG Wire

This document was generated on 03/30/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION