

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0191600002](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Closed-End Insulated Splice for 10-16 AWG Wire

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-19408-109 (PDF)</a>
<a href="#">Product Specification PS-19902-013 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR18689
UL	E32244

**General**

Product Family	Splices
Series	<a href="#">19160</a>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
MolexKits	Yes
Overview	<a href="#">Splices</a>
Product Name	Closed-End Insulated
UPC	800753110144

**Physical**

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.041/g
Packaging Type	Bag
Temperature Range - Operating	105°C
Wire Insulation Diameter	9.65mm max.
Wire Size AWG	10, 12, 14, 16

**Electrical**

Voltage - Maximum	600V
-------------------	------

**Material Info**

Old Part Number	NC-1610
-----------------	---------

**Reference - Drawing Numbers**

Packaging Specification	PK-19408-109
Product Specification	PS-19902-013
Sales Drawing	SD-19160-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/108/2014 (17 Dec  
2014)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[19160 Series](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are  
found by selecting the products below.  
Crimp Height Specifications are then  
contained in the Application Tooling  
Specification document.*

**Global**

Description	Product #
Hand Crimp Tool	<a href="#">0640010600</a>
Crimp Head for the AT-200™ Pneumatic Hand Tool	<a href="#">0640050600</a>
Crimp Head for the AT-200™ Pneumatic Hand Tool, Crimp from Top	<a href="#">0640053500</a>

This document was generated on 04/13/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**