

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191640043](#)
Status: **Active**
Overview: [Splices](#)
Description: Perma-Seal™ Step Down Butt Splice for 14-16 AWG to 18-22 AWG Wire

Documents:

Drawing (PDF)	Product Specification PS-19902-013 (PDF)
Product Specification PS-19902-011 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Splices
Series	19164
Comments	Step down: 14/16 to 18/22 AWG
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Splices
Product Name	Butt - Step Down, Perma-Seal™
UPC	800753113282

Physical

Barrel Type	Closed
Color - Resin	Blue
Insulation	NiAc™
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	2.916/g
Packaging Type	Bag
Temperature Range - Operating	-55°C to +125°C
Wire Insulation Diameter	5.84mm max.
Wire Size AWG	14, 16, 18, 20, 22

Electrical

Voltage - Maximum	600V
-------------------	------

Material Info

Old Part Number	SBA-631
-----------------	---------

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	SD-19164-029



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[19164 Series](#)

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Power Crimp Tool Head for Terminals 10-22 AWG Wire	0640057400
PremiumGrade™ Hand Crimp Tool	0640017400