


U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINDICHT® SM-M	13.01.2016

SKINDICHT® SM-M, metric counter nuts for through-holes on thin-walled housings



Good chemical resistance



Mechanical resistance



Application range

Used when a gland has to be countered, or in through-holes on thin-walled housings

Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Classification:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 Class-Description: Locknut for cable screw gland

Material:

Nickel-plated brass

Temperature range:

-20°C to +100°C

Product Management	Document: LAPP_PRO1025EN.pdf	1 / 2
--------------------	------------------------------	-------

**SKINDICHT® SM-M**

13.01.2016

Part number	Article designation / size	Thickness (mm)	SW wrench size mm	Outer Ø (mm)
SKINDICHT® SM-M				
52103000	12 x 1,5	3.0	15	16,5
52103010	16 x 1,5	3.0	19	20,9
52103020	20 x 1,5	3,5	24	26,4
52103030	25 x 1,5	4.0	30	33.0
52103040	32 x 1,5	4.0	36	39,6
52103050	40 x 1,5	5.0	46	50,6
52103060	50 x 1,5	5.0	60	65.0
52103070	63 x 1,5	5.0	70	77.0
52103071	75 x 1,5	8.0	85	95.0
52103072	90 x 2	10.0	102	114.0
52103073	110 x 2	12.0	124	135.0