

Product data sheet

Characteristics

27109

voltage release - MX + OF - 1 NO/NC 110..277 V
AC - 110...130 V DC - for C60

Product availability: Stock - Normally stocked in distribution facility

Price*: 140.00 USD



Main

Commercial Status	Commercialised
Range of product	C60
Device short name	MX + OF
Product or component type	Shunt trip release with OC contact
Signal contacts composition	1 C/O
[Ie] rated operational current	0.8 A AC 50/60 Hz 240 V 0.4 A AC 50/60 Hz 120 V 0.3 A DC 125 V 0.3 A DC 110 V 1 A AC 50/60 Hz 277 V
Control circuit voltage	110...277 V AC 50/60 Hz 110...130 V DC
9 mm pitches	2

Complementary

Impulse duration	8 ms
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	3.25 in (82.5 mm)
Width	0.71 in (18 mm)
Depth	2.68 in (68 mm)
Connections - terminals	Pad terminal 1 cable(s) 0 in ² (2.5 mm ²) flexible
Wire stripping length	0.35 in (9 mm)
Tightening torque	8.85 lbf.in (1 N.m)

Environment

Standards	EN/IEC 60947-5-1 UL 489
Product certifications	ASEFA ASTA KEMA LCIE
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 131 °F (55 °C)
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

Ordering and shipping details

Category	00908 - C60N SUPP PROTECTORS
Discount Schedule	DE2
GTIN	00785901834472
Nbr. of units in pkg.	1
Package weight(Lbs)	0.16

Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	BE

Contractual warranty

Period	18 months
--------	-----------