



Schneider Electric USA
1415 South Roselle Road
Palatine, IL 60067
Customer Care Center: 1-888-778-2733
Web: www.schneider-electric.us

ITEM # ZB5AVB5, BASE & LIGHT MODULE

Base & Light Module

Specifications	
Product Description	Base & Light Module
Ampere Rating	N/A
Terminal Type	Screw Clamp
Wire Range	min: 1x0.22; max: 2x16AWG
Tightening Torque	0.8 Nm
Light Module Electrical Consumption	24V = 18mA; 120/240V = 14mA
CE	Yes
RoHS	Yes
Contact Configuration	n/a
Contact Material	n/a
Light Module Supply Voltage	24Vac/dc
Light Module Type	LED(yellow)
Light Module Voltage	24Vac/dc
Utilization Category	n/a
Used On	ZB5 Plastic Operators
Application	n/a