

# Product data sheet

## Characteristics

# 7B1N

## 9007MS/ML limit switch lever - zinc - fixed length - outside nylon roller

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 13.60 USD

### Main

Commercial Status	Commercialised
Range of product	9007
Series name	Miniature potted
Product or component type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007MS04.. 9007ML04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 1.5 in -
Type of roller	1 nylon outside roller diameter: 0.75 in - width: 0.5 in
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Tracks	1.375 in
Switch actuation	By 30° cam
Product weight	0.1 lb(US)

### Environment

Ambient air temperature for operation	-40...221 °F
Ambient air temperature for storage	-40...221 °F
Environmental characteristic	Standard environment

### Ordering and shipping details

Category	22421 - LIMIT SWITCHES,ARMS FOR 9007MS
Discount Schedule	T
GTIN	00785901216087
Nbr. of units in pkg.	1
Package weight(Lbs)	0.10
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	MX

### Contractual warranty

Period	18 months
--------	-----------