

**ITEM # VM1PNOQ, ULTRASONIC SENSOR, DISCRETE, 18 MM SNOOT DUAL MOUNT, 12-24 VDC**

- Ø18 mm mountable or flat profile mountable sensors for various mounting needs
- Discrete proximity, analog or dual-level sensing
- UL, CE, RoHS



Specifications

<b>Length</b>	2.35 in
<b>Width</b>	0.71 in
<b>Depth</b>	1.72 in
<b>Face Material</b>	Glass Epoxy
<b>Body Style</b>	Dual Mount
<b>Volts Type</b>	DC
<b>Voltage Range</b>	12-24 VDC
<b>Current Consumption</b>	40 mA
<b>Circuit Type</b>	Normally Open
<b>Output Mode</b>	PNP
<b>Temp Range</b>	-30° to 70° C (-22° to 158° F)
<b>Max Load</b>	100 mA
<b>Sensing Range</b>	50.8 to 508 mm (2.0 to 20.0 in)
<b>Response Time</b>	15 ms
<b>Sonic Frequency</b>	300 kHz

<b>Field Configurable</b>	No
<b>DeviceNet</b>	No
<b>NEMA Type</b>	4X (indoor use only)
<b>Connector Type</b>	M12
<b>Standards</b>	UL, CE Rohs
<b>Special Features</b>	Tamper Proof with PB100 Pushbutton Accessory
<b>IP Rating</b>	IP67