



Product availability: Stock - Normally stocked in distribution facility

Price*: 39.80 USD

Main

Commercial Status	Commercialised
Product or component type	Miniature circuit-breaker
Range of product	QO
Line Rated Current	15 A
Product certifications	CSA UL listed
System Voltage	120/240 V AC
Mounting mode	Bolt-on
Poles description	1P
Short-circuit current	10 kA
Number of spaces required	1
Circuit breaker type	Standard
Circuit breaker application	HACR and Switching Duty rated
Electrical connection	Pressure plate
AWG gauge	AWG 14...AWG 8 (copper or aluminium)
Accessory / separate part type	None

Ordering and shipping details

Category	00015 - QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901416708
Nbr. of units in pkg.	10
Package weight(Lbs)	0.28
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------