

# 2510FG6

## MANUAL STARTER 277VAC

Product availability: Stock - Normally stocked in distribution facility

Price\*: 116.00 USD

### Main

Commercial Status	Commercialised
Product or component type	Single Unit Manual Starter
Range of product	F
[In] rated current	16 A
Product certifications	CE CSA UL listed
Cable entry	0.5" and 0.75" knock-outs (top and bottom)
NEMA degree of protection	NEMA 1 plastic standard size
Motor power hp	0.75 hp 230 V DC 0.75 hp 115 V DC 1 hp 277 V AC 1 hp 230 V AC 1 hp 115 V AC
[Ue] rated operational voltage	230 V DC 277 V AC
Poles description	2P
Control type	Toggle switch (with lock-off)
Network number of phases	1 phase
Local signalling	No indicator
Reset	Manual
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
Thermal overload type	Melting alloy

### Ordering and shipping details

Category	21101 - 2510,2511,2512 F
Discount Schedule	CP1
GTIN	00785901554035
Nbr. of units in pkg.	3
Package weight(Lbs)	0.82
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will not be Compliant
REACH	Reference not containing SVHC above the threshold

### Contractual warranty

Period	18 months
--------	-----------