

# Product data sheet

## Characteristics

# QO116M100

## LOADCTR QO MB 240V 100A 1PH 16SP NEMA 1

Product availability: Stock - Normally stocked in distribution facility

Price\*: 342.00 USD



### Main

Commercial Status	Commercialised
Product or component type	Load Centre
Range of product	QO
Load centre type	Convertible Mains (breaker)
Line Rated Current	100 A
Number of spaces	16
Short-circuit current	22 kA
Number of circuits	16
Number of tandem circuit breakers	0
Phase	1 phase
System Voltage	120/240 V AC

### Complementary

AWG gauge	AWG 6...AWG 1 (aluminium/copper)
NEMA degree of protection	NEMA 1 indoor
Cover type	Order separately
Device composition	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire
Material	Tin plated copper busbar
Product certifications	UL listed

### Ordering and shipping details

Category	00001 - QO 1PH LC,12-42 CKT,NEMA1
Discount Schedule	DE3A
GTIN	00785901847748
Nbr. of units in pkg.	1
Package weight(Lbs)	11.69
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	US

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1411 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Period	18 months
--------	-----------