

87 0 | KNIPEX Cobra® Hightech Water Pump Pliers

with tether attachment point

DIN ISO 8976



87 02 180 T



- push the button for adjustment on the workpiece
- fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- box-joint design for high stability due to double guide
- reliable catching of the hinge bolt: no unintentional shifting
- guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, oil-hardened

87 02 180 T:

- Pliers with tether attachment point for mounting a fall protection

87 02 300 T:

- Pliers with tether attachment point for mounting a fall protection

87 02 250 T:

- Pliers with tether attachment point for mounting a fall protection

KNIPEX Cobra® - the Hightech Water Pump Pliers. No more time-consuming presetting of the required opening size. Just position the upper jaw to the workpiece, push button and move close the lower jaw, ingeniously simple.

Article No.	EAN 4003773-		Pliers	Head	Handles	Ø Inch	Ø mm	mm	Adjustment positions	mm	g
87 02 180 T	080145		grey atramentized	polished	with multi-component grips	1 1/2	42	36	18	180	200
87 02 300 T	080169		grey atramentized	polished	with multi-component grips	2 3/4	70	60	30	300	600
87 02 250 T	080152		grey atramentized	polished	with slim multi-component grips	2	50	46	25	250	370


technical change and errors excepted



Fine adjustment by pushing a button: fast and comfortable.



Fast and firm adjustment directly on the workpiece



Teeth set against the direction of rotation have a self-locking effect and prevent slipping on the workpiece.

