

# 97 54 Crimping Pliers for micro plugs parallel crimping



97 54 24



- parallel crimping performance to satisfy the particularly high standards of small connectors
- repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- fixed locator for D-Sub micro plugs for an exact positioning of connector and cable
- crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- crimping pliers for other mini plugs such as HD 22, Modu IV, Micro Timer, MQS ... on request
- Chrome vanadium electric steel in special quality, oil-hardened

Article No.	EAN 4003773-				Pliers	Handles	Applications	Capacity mm <sup>2</sup>	AWG	Number of crimping positions	mm	g
97 54 24	060215				burnished	with multi-component grips	D Sub; HD 20; HDE plug	0,03 - 0,56	32 - 20	3	190	305
97 54 25	079859				burnished	with multi-component grips	For Micro-Fit™		26 - 20	3	190	305
97 54 26	079866				burnished	with multi-component grips	For Mini-Fit®		20 - 16	3	190	305
97 54 27	079873				burnished	with multi-component grips	For MQS connectors	0,25 / 0,35 / 0,5		3	190	305

technical change and errors excepted

