

## DIN rail bus connectors - HBUS 107,6-16P-1S BK - 2896306


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plug component, Nominal current: 3 A, Number of positions: 16, Pitch: 2.54 mm, Color: jet black



### Key Commercial Data

Packing unit	10 pc
GTIN	 4 046356 096744
Weight per Piece (excluding packing)	30.8 g
Custom tariff number	85369010
Country of origin	Germany
Product key	ACHBBA

### Technical data

#### General

Housing material	Polyamide
Color	black

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (Depends on the derating curve)
---------------------------------	---

#### Dimensions

Length	37.1 mm
Width	107.6 mm
Pitch	2.54 mm

#### Technical data

Connection in acc. with standard	CUL
Nominal voltage $U_N$	60 V
Nominal current $I_N$	2 A
Indicator1	CUL1
Flammability rating according to UL 94	V0

# DIN rail bus connectors - HBUS 107,6-16P-1S BK - 2896306

## Technical data

### Technical data

Number of positions	16
---------------------	----

### Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440309

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002638

### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals

### Approvals

---

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

---

### Ex Approvals

---

Approvals submitted

---

## DIN rail bus connectors - HBUS 107,6-16P-1S BK - 2896306

### Approvals

#### Approval details

UL Recognized	
Nominal current IN	2 A
Nominal voltage UN	60 V

cUL Recognized	
Nominal current IN	2 A
Nominal voltage UN	60 V

EAC
-----

cULus Recognized
------------------

### Accessories

#### Accessories

##### Filler plug

Printed-circuit board connector - HBUS-B SET BK - 2278173



Set of 3 caps, for protecting unused DIN rail bus connectors, simply snap on to fit

Electronic housing - BSL-2,54/16-ST 40CM - 2202938



Cable bridge for cross-DIN-rail connection of the HBUS connector

## DIN rail bus connectors - HBUS 107,6-16P-1S BK - 2896306

### Accessories

Electronic housing - BSL2-2,54/16-ST - 2201281



Cable bridge for cross-DIN-rail connection of the HBUS connector

---

Power plug - SL2-2,54/16-ST - 2896348



Power connector for DIN rail bus connector with 16 free cable ends with a cross section of 0.25 mm<sup>2</sup>, 500 mm long, male contacts

---

Power plug - BL2-2,54/16-ST - 2896335



Power connector for DIN rail bus connector with 16 free cable ends with a cross section of 0.25 mm<sup>2</sup>, 500 mm long, female contacts

---

### Necessary add-on products

PSTD 0,65X0,65/9-2,54 - 2200700




Pin strip (horizontal)

---

### Drawings

## DIN rail bus connectors - HBUS 107,6-16P-1S BK - 2896306

Dimensional drawing



A=107.6 mm

---

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>