

## T5 Short Standard / Luxline® Plus

F13W/T5/135

**0000030**



### Range Features

- 



### PRODUCT OVERVIEW

Lamp finish	Coated
Lamp shape	Linear
Colour temperature (K)	3500
CRI (Ra)	64
EAN code	5410288000305
Energy class	A
Cap/Base	G5
Type	T5 Standard Short
Watt (Nominal) (W)	13
Light colour	535 White
Ordering number	0000030
Efficacy (Rated) (lm/w)	67
Average life (Rated) (h)	7500
Luminous flux (Rated) (lm)	880
Technology	Fluorescent
Voltage (V)	95

### DATA TABLE

#### General data

Average life (Nominal) (h)	10000
Control gear required	Yes
Lamp finish	Coated
Lamp shape	Linear
EAN code	5410288000305
Energy class	A
Fixture rating	Open
General application	Retail;Hospitality;Logistics and Industry;Museums;Education;Office;Residential & Consumer;
IEC Reference	IEC 60081
IEC Reference 2	IEC 61195

# T5 Short Standard / Luxline® Plus

F13W/T5/135

**0000030**

<b>Intended purpose</b>	General lighting
<b>Cap/Base</b>	G5
<b>Lamp mercury content (mg)</b>	2.3
<b>Type</b>	T5 Standard Short
<b>Ordering number</b>	0000030
<b>Product name</b>	F13W/T5/135
<b>Average life (Rated) (h)</b>	7500
<b>Rated survival factor at 2000 h 50Hz</b>	1
<b>Rated survival factor at 4000 h 50Hz</b>	0.99
<b>Rated survival factor at 6000 h 50Hz</b>	0.96
<b>Rated survival factor at 8000 h 50Hz</b>	0.83
<b>Special purpose lamp</b>	No
<b>Technology</b>	Fluorescent
<b>Transformer required</b>	No
<b>Sales pack quantity</b>	25
<b>E-number FI</b>	4940239

## Optical data

<b>Colour temperature (K)</b>	3500
<b>CRI (Ra)</b>	64
<b>Light colour</b>	535 White
<b>Luminous flux (Nominal) (lm)</b>	880
<b>Rated lumen maint. factor at 2000 h 50Hz</b>	0.88
<b>Rated lumen maint. factor at 4000 h 50Hz</b>	0.82
<b>Rated lumen maint. factor at 6000 h 50Hz</b>	0.78
<b>Rated lumen maint. factor at 8000 h 50Hz</b>	0.75
<b>Luminous flux (Rated) (lm)</b>	880

## Electrical data

<b>Current (A)</b>	0.165
<b>Ignition voltage (V)</b>	0
<b>kWh per 1000 hours burning time</b>	15
<b>Watt (Nominal) (W)</b>	13
<b>Efficacy (Rated) (lm/w)</b>	67
<b>Rated lamp efficacy (lm/W) 100H 50Hz at optimum temp.</b>	69
<b>Watt (Rated) - High frequency (W)</b>	13
<b>Voltage (V)</b>	95

## T5 Short Standard / Luxline® Plus


F13W/T5/135

**0000030**

### Physical data

<b>Diameter (mm)</b>	16
<b>Max. Lamp Diameter (mm) - D</b>	16
<b>Lamp Length (mm) - C/L</b>	531.1
<b>Length base to base (mm) - A</b>	516.9
<b>Length base to pin Min-Max - B</b>	521.6-524.0
<b>Single packaging type</b>	Box/Sleeve
<b>Weight (kg)</b>	0.04
<b>Outer package dimensions (L x W x H) (cm)</b>	54.80 x 11.00 x 10.50
<b>Single package dimensions (L x W x H) (cm)</b>	53.20 x 1.90 x 1.90

### TECHNICAL DRAWINGS



## T5 Short Standard / Luxline® Plus

F13W/T5/135

0000030

