


SCA1000-D01



Appearance & Shape



Packaging Information

Packaging	Specifications	Minimum Order Quantity
-1	330mm Embossed Tape	100

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
 2.This datasheet has only typical specifications because there is no space for detailed specifications.
 Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

SCA1000-D01

Specifications

Output Type	Analog/SPI
Axis	2
Maximum Angular Velocity	±1.7g
Supply Voltage Range	5V to
Offset Temp. Characteristic	±100mg
Sensitivity	1.2V/G
Amplitude Response	50Hz
Mass	1.01g

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.