

Datasheet

Art.No. 70.325.1028.0

Bottom BAS GUT GE 10 50 A

revos BASIC 500V size 10 open-bottom base, with cover, double locking lever



Approvals



Technical data

General

Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	10
Model	Equipment mounted (feed-through)
Locking mechanism	Double locking levers
Cable entry	None
Type of cable	None
With cable screw gland	No
Hinged lid	Yes
EMC-version	No

Classification

ECLASS 8.1	27440202: Housing for industrial connectors
ETIM 5.0	EC000437: Housing for industrial connectors
ETIM 4.0	EC000437: Housing for industrial connectors
ETIM 3.0	EC000437: Housing for industry plug connectors