

4W LED Candle

4W B22/E14/E27 LED Candle Lamp



Features

- Save energy up to 85% compared with filament lamp.
- Direct replacement of B22, E14 or E27 lamp.
- High lumen output.
- Long life of 20,000h.
- Instant start.
- No UV output.
- Mercury free.

Safety and Maintenance

- Switch off supply and allow cooling before handling lamp.
- Use in totally enclosed fittings will reduce lamp life.
- Do not dispose of lamp in household waste.
- Dispose of in appropriate section of local civic amenity site or recycling centre.



Specifications – 3000K

Product Code	RLCND04B22-30-N	RLCND04E14-30-N	RLCND04E27-30-N
Lamp Cap	B22	E14	E27
Lamp Shape	Candle	Candle	Candle
Nominal Power (W)	4	4	4
Voltage	220-240Vac 50-60Hz	220-240Vac 50-60Hz	220-240Vac 50-60Hz
Current (mA)	33	33	33
Nominal Luminous Flux (lm)	320	320	320
CCT (K)	3000K Warm White	3000K Warm White	3000K Warm White
Nominal Lifetime (h)	20000	20000	20000
Dimmable	No	No	No
Switching Cycles	50000	50000	50000
Warm-up time to 60% (S)	Instant full light	Instant full light	Instant full light
Length (mm)	99	102	100
Diameter (mm)	39	39	39
Mercury (mg)	0	0	0
Clean-up instructions	N/A	N/A	N/A
Retrofit	No	Yes	No
Equivalent Wattage (W)	30	30	30
Rated Power (W)	4.0	4.0	4.0
Rated Luminous Flux (lm)	320	320	320
Rated Lifetime (h)	20000	20000	20000
Power Factor	0.52	0.52	0.52
Rated Peak Candelas (cd)	30	30	30
LMF at Nominal Lifetime	0.75	0.75	0.75
SDCM of CCT	<6	<6	<6
CRI	83	83	83
Start Time (s)	0.45	0.45	0.45
Temperature Range (°C)	-20 to 40	-20 to 40	-20 to 40

Energy Label – 3000K

Manufacturer	REON	REON	REON
Product Code	RLCND04B22-30-N	RLCND04E14-30-N	RLCND04E27-30-N
Energy Class	A+	A+	A+
Energy Consumption (kWh/1000h)	4	4	4

Product Markings – 3000K

Manufacturer	REON	REON	REON
Product Code	RLCND04B22-30-N	RLCND04E14-30-N	RLCND04E27-30-N
Voltage	220-240Vac 50-60Hz	220-240Vac 50-60Hz	220-240Vac 50-60Hz
Nominal Power (W)	4	4	4
Current (mA)	33	33	33
CE Mark	Yes	Yes	Yes
WEEE Mark	Yes	Yes	Yes
Batch Code	Yes	Yes	Yes



Specifications – 4000K

Product Code	RLCND04B22-40-N	RLCND04E14-40-N	RLCND04E27-40-N
Lamp Cap	B22	E14	E27
Lamp Shape	Candle	Candle	Candle
Nominal Power (W)	4	4	4
Voltage	220-240Vac 50-60Hz	220-240Vac 50-60Hz	220-240Vac 50-60Hz
Current (mA)	33	33	33
Nominal Luminous Flux (lm)	340	340	340
CCT (K)	4000K Cool White	4000K Cool White	4000K Cool White
Nominal Lifetime (h)	20000	20000	20000
Dimmable	No	No	No
Switching Cycles	50000	50000	50000
Warm-up time to 60% (S)	Instant full light	Instant full light	Instant full light
Length (mm)	99	102	100
Diameter (mm)	39	39	39
Mercury (mg)	0	0	0
Clean-up instructions	N/A	N/A	N/A
Retrofit	No	Yes	No
Equivalent Wattage (W)	31	31	31
Rated Power (W)	4.0	4.0	4.0
Rated Luminous Flux (lm)	340	340	340
Rated Lifetime (h)	20000	20000	20000
Power Factor	0.52	0.52	0.52
Rated Peak Candelas (cd)	32	32	32
LMF at Nominal Lifetime	0.75	0.75	0.75
SDCM of CCT	<6	<6	<6
CRI	83	83	83
Start Time (s)	0.45	0.45	0.45
Temperature Range (°C)	-20 to 40	-20 to 40	-20 to 40

Energy Label – 4000K

Manufacturer	REON	REON	REON
Product Code	RLCND04B22-40-N	RLCND04E14-40-N	RLCND04E27-40-N
Energy Class	A+	A+	A+
Energy Consumption (kWh/1000h)	4	4	4

Product Markings – 4000K

Manufacturer	REON	REON	REON
Product Code	RLCND04B22-40-N	RLCND04E14-40-N	RLCND04E27-40-N
Voltage	220-240Vac 50-60Hz	220-240Vac 50-60Hz	220-240Vac 50-60Hz
Nominal Power (W)	4	4	4
Current (mA)	33	33	33
CE Mark	Yes	Yes	Yes
WEEE Mark	Yes	Yes	Yes
Batch Code	Yes	Yes	Yes



Specifications – 6500K

Product Code	RLCND04B22-65-N	RLCND04E14-65-N	RLCND04E27-65-N
Lamp Cap	B22	E14	E27
Lamp Shape	Candle	Candle	Candle
Nominal Power (W)	4	4	4
Voltage	220-240Vac 50-60Hz	220-240Vac 50-60Hz	220-240Vac 50-60Hz
Current (mA)	33	33	33
Nominal Luminous Flux (lm)	360	360	360
CCT (K)	6500K Day Light	6500K Day Light	6500K Day Light
Nominal Lifetime (h)	20000	20000	20000
Dimmable	No	No	No
Switching Cycles	50000	50000	50000
Warm-up time to 60% (S)	Instant full light	Instant full light	Instant full light
Length (mm)	99	102	100
Diameter (mm)	39	39	39
Mercury (mg)	0	0	0
Clean-up instructions	N/A	N/A	N/A
Retrofit	No	Yes	No
Equivalent Wattage (W)	33	33	33
Rated Power (W)	4.0	4.0	4.0
Rated Luminous Flux (lm)	360	360	360
Rated Lifetime (h)	20000	20000	20000
Power Factor	0.52	0.52	0.52
Rated Peak Candelas (cd)	35	35	35
LMF at Nominal Lifetime	0.75	0.75	0.75
SDCM of CCT	<6	<6	<6
CRI	81	81	81
Start Time (s)	0.45	0.45	0.45
Temperature Range (°C)	-20 to 40	-20 to 40	-20 to 40


Energy Label – 6500K

Manufacturer	REON	REON	REON
Product Code	RLCND04B22-65-N	RLCND04E14-65-N	RLCND04E27-65-N
Energy Class	A+	A+	A+
Energy Consumption (kWh/1000h)	4	4	4

Product Markings – 6500K


Manufacturer	REON	REON	REON
Product Code	RLCND04B22-65-N	RLCND04E14-65-N	RLCND04E27-65-N
Voltage	220-240Vac 50-60Hz	220-240Vac 50-60Hz	220-240Vac 50-60Hz
Nominal Power (W)	4	4	4
Current (mA)	33	33	33
CE Mark	Yes	Yes	Yes
WEEE Mark	Yes	Yes	Yes
Batch Code	Yes	Yes	Yes

Dimensions




Photometric Information

3000K



4000K



6500K

