

### 3-Port Portable USB 3.0 Hub plus Gigabit Ethernet - Aluminum with Built-in Cable

StarTech ID: ST3300GU3B



The ST3300GU3B Portable USB 3.0 Hub features an integrated GbE port, enabling you to expand your laptop connectivity by adding three external USB 3.0 ports, as well as a Gigabit network port via a single USB 3.0 connection. This hub is an ideal laptop accessory for your Microsoft Surface™ Pro 4, Surface Pro 3, Surface Book, Dell™ XPS 13, and many other devices.

The hub merges Gigabit network support and USB 3.0 hub access into lightweight yet sturdy aluminum casing, providing vital connectivity ports that are often limited or nonexistent on modern mobile computers, while remaining compact and travel-friendly. Plus, with an attached USB 3.0 host connection cable there's no need to carry a separate cable with you, so you can tuck the hub neatly into your laptop bag for maximum portability.

For faster and more consistent network connections, the integrated Ethernet port leverages the 5 Gbps capabilities of the USB 3.0 interface to provide wired Gigabit access that is fully compatible with IEEE 802.3/u/ab standards.

An ideal laptop accessory, this mobile USB hub is great for connecting low-power peripherals like a mouse, keyboard or USB flash drive, and also includes a universal power adapter for connecting devices such as [external hard drive enclosures](#).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Applications

- Work from your Ultrabook, laptop or netbook easily while you're on the run or on the road, the perfect travel accessory with more connectivity options
- An ideal laptop accessory for Microsoft Surface Pro 4, Surface Pro 3, Surface Book, Dell XPS 13, Dell Latitude 11 5000 Series 2-in-1 and other devices
- Connect a wide variety of peripherals at home / office to a laptop, all from a single USB 3.0 connection
- Add Gigabit support to your laptop for use in boardrooms, hotels, classrooms, offices, or home environments
- Replace a failed built-in Ethernet port on a laptop, or upgrade to 1000 Mbps Gigabit connectivity

## Features

- Provides three USB 3.0 hub ports, with support for up to 5 Gbps
- Gigabit Ethernet RJ-45 port through a single USB 3.0 connection
- Aluminum casing with a compact, slim, and lightweight design for maximum portability
- Dongle-style combination adapter with built-in USB 3.0 cable
- IEEE 802.3, IEEE 802.3u, IEEE 802.3ab, IEEE 802.3az compatible
- Supports 10/100/1000 Mbps half and full-duplex operation
- Backward compatible with USB 2.0 and 1.x devices
- Universal Power Adapter (NA/UK/EU) included

**Technical Specifications**

Warranty	2 Years
Bus Type	USB 3.0
Chipset ID	Genesys Logic - GL3522 (USB 3.0) ASIX - AX88179 (LAN)
Fast-Charge Port(s)	No
Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab
Industry Standards	IEEE 802.3az Energy-Efficient Ethernet, IEEE 802.3x Flow Control, 802.1q VLAN Tagging, 802.1p Layer 2 Priority Encoding
Industry Standards	USB 3.0 - Backward compatible with USB 2.0 and 1.1
Interface	USB 3.0
Interface	USB 3.1 Gen 1
Interface	RJ45 (Gigabit Ethernet)
Ports	3
USB-C Device Port(s)	No
USB-C Host Connection	No
Auto MDIX	Yes
Auto-Negotiation	Yes
Compatible Networks	10/100/1000 Mbps
Flow Control	Full duplex flow control
Full Duplex Support	Yes
Jumbo Frame Support	4K max.
Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
Type and Rate	USB 3.0 - 5 Gbit/s
Connector Type(s)	3 - USB Type-A (9 pin) USB 3.0 Female
Connector Type(s)	1 - RJ-45 Female
Connector Type(s)	1 - USB Type-A (9 pin) USB 3.0 Male
OS Compatibility	Windows® 10 (32/64), 8 / 8.1 (32/64), 7 (32/64), Vista (32/64), XP (32/64) Windows Server® 2012, 2008 R2, 2003 Mac OS® 10.6 and later (tested up to 10.11) Chrome OS™ Linux 2.6.x and later (tested up to 3.17)
<b>Note</b>	If connected to a USB 2.0 host port, performance may be limited
System and Cable	Available USB 3.0 port

Requirements

LED Indicators	1 - Link
LED Indicators	1 - Activity
Center Tip Polarity	Positive
Input Current	300 mA
Input Voltage	100 ~ 240 AC
Output Current	2 A
Output Voltage	5 DC
Plug Type	H
Power Consumption	10 W Max.
Power Source	AC Adapter Included
Humidity	0~85% RH (Non-Condensing)
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-10°C to 75°C (14°F to 167°F)
Cable Length	148 mm [5.8 in]
Color	Black
Enclosure Type	Aluminum
Form Factor	Compact
Product Height	14 mm [0.6 in]
Product Length	87 mm [3.4 in]
Product Weight	62 g [2.2 oz]
Product Width	43 mm [1.7 in]
Package Quantity	1
Shipping (Package) Weight	366 g [12.9 oz]
Included in Package	1 - Aluminum USB 3.0 Hub w/ GbE Adapter
Included in Package	1 - Universal Power Adapter (NA/EU/UK/AU)
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

