


# NITRO 4X

4/8/16 CHN 1080P HI-DEF TVI, AHD, 960H, IP - NVR

## NITRO 4x

4/8/16 CHANNEL 1080P HI-DEF NVR



### 4 In 1 Formats

This NVR supports High-Definition Transport Video (HD-TVI), Analogue High Definition (AHD), 960H and Internet Protocol (IP) recording formats.



### Widescreen Footage

1080P formatting also means that images are recorded in a widescreen format which suits modern TV's and monitors, meaning images do not get stretched or squeezed to fit on screen.



### Scheduled Recording

Set the NVR to record at specific times of the day or for set periods when you are at work, away for weekends or on holiday.

SMART PHONE  
COMPATIBLE APP



HDMI

Full HD  
1080P



## NITRO 4X NVR KEY FEATURES

- P2P No port forwarding
- Real time 1080P recordings
- HDMI/VGA monitor outputs
- PTZ control
- USB backup
- Motion detection
- 4 channel playback
- 4 alarm inputs
- Arc compatible
- All in one NVR



1080P  
1920 X 1080



720P  
1280 X 720



960H  
960 X 576

# NITRO 4X

4/8/16 CHN 1080P HI-DEF TVI, AHD, 960H, IP - NVR



Model	4 Channel	8 Channel	16 Channel
<b>VIDEO</b>			
Video codec	H.264		
Encode	4*720P/4*1080P@15fps	8*720P/8*1080P@12fps	16*1080N/16*1080P@12fps
Decode	4*720P/4*1080P@15fps	8*720P/4*1080P@12fps	16*1080N/16*1080P@12fps
Multi-mode input	Pure Analog: 4*1080P Pure Network: 8*1080P; 8*960P;4*3M ;	Pure Analog: 8*1080P Pure Network: 8*1080P; 16*960P;4*3M ;4*5M	Pure Analog: 16*1080P; 16*1080N; 8*1080P; Mixed: 8*1080P (local) +8*1080P (IP) Pure Network: 8*1080P+8*960P; 8*3M; 4*5M
Onvif	support		
<b>AUDIO</b>			
Audio compression	G.711A		
Intercom	support		
<b>RECORDING AND PLAYBACK</b>			
Record mode	Manual>alarm>motion detection>timing		
Playback Channels	4 (pure local input mode)	4 (pure local input mode)	16 (pure local input mode)
<b>STORAGE</b>			
Backup mode	Network backup, USB HDD, USB writer, SATA writer		
<b>INTERFACE</b>			
Video input	4 BNC	8 BNC	16 BNC
Video output	1ch VGA, 1ch HDMI		
Audio input	4ch RCA	8ch RCA	6ch RCA
Audio output	1ch RCA		
Alarm input	4		
Alarm output	1		
Network interface	RJ45 10M/100M Adaptive Ethernet port		
PTZ control	RS485; support multiple PTZ protocols		
USB	2 USB ports		
Hard disk	1 SATA (Each maximum support 6T)		
Wireless	3G, WIFI (expand via USB)		
Power	12V/2A		
Dimension	310mm (length) x 230mm (width) x 44mm (height)		

