

Integrated 2-Channel Zone Amplifier (Audio Only)



The AU-A50 is a compact 2 channel digital zone amplifier that is perfect for providing high quality audio distribution into remote AV zones within any multi-room installation. This advanced solution can integrate digital and analogue audio signals from multiple sources, including an audio output from a TV, enabling sound re-enforcement within any zone.

FEATURES

- 30W per channel digital stereo Amplifier
- Control via remote control, RS-232 or IP (Web GUI or Telnet)
- Single zone amplifier
- LCD Display
- Compact design for remote in-zone application

SPECIFICATIONS

Input:

- 1x RCA (1x Coaxial 2 Channel LPCM),
- 1x Toslink (1x Optical 2 Channel LPCM)
- 2x RCA (1x Analogue Stereo (L/R))
- 1x 3.5mm Stereo mini-jack (1x Analogue Stereo(L/R))
- 1x RJ45 (1x IP Control)
- 1x RJ45 (1x Keypad - Reserved for future use - Propriety Data)
- 1x 3.5mm Stereo mini-jack (1x Infra Red Receiver)
- 1x USB Type A (1x Service Port Propriety Data)

Output: 4x Speaker Binding Posts (1x Speaker Level Stereo Output)

Power: 24V DC (US/EU standards, CE/FCC/UL certified)

Dimensions: 215mm (W) x 150mm (D) x 50mm (H)

Gross Weight: 1680g

Net. Weight: 1380g

Packaging: Boxed

