



**GREENLEE.**  
A Textron Company

MADE FOR THE TRADE!™



CRIMPER 1600 OPEN BARREL AWG 24-14

Open Barrel Contact Pin Crimper

Cat No: 52049994

UPC No: 769328100730

### Description

---

- Professional crimping tool for open-barrel box and round connector contacts with a wire range of 24-14 AWG (0.2-2.5 mm<sup>2</sup>)
- Precision fixed dual-plate dies for crimp accuracy
- Built-in locator
- Crimps non-insulated terminal lugs, cable lugs and parallel and serial splices or F-Type
- Works with Molex, Waldom & Leoco-type connectors
- Durable steel construction for long life
- Rubber-embedded ergonomic handles for low-effort operation

### Specifications

---

- Application : For Open-Barrel Box And Round Connector Contacts With A Wire Range Of 24-14 AWG (0.200 - 2.500 SQ-MM)
- Crimping Range : Small: 24-22 AWG (0.050 - 0.200 SQ-MM), Medium: 18-14 AWG (0.340 - 0.750 SQ-MM)
- Handle Type : Rubber Embedded Ergonomic
- Material : Durable Steel
- Type : Open Barrel Contact Pin
- Weight : 14.000 OZ (400.000 GM)