




SOFT CAPS - LANYARD WITH CORD

FIGURE 4



Size	Plug		Receptacle				A	D1	L	d	D	Part number	Fig.
	UP01	UP50	UR01	UR02	UR03	UR50							
07	●						18.5	11.0	200	-	-	UCP07C 1A1 A200	1
			○	○	●	●	16.0	11.0	200	-	-	UCR07C 1A1 A200	2
		●					12.8	11.0	200	-	-	UCP07P 1A1 A200	3
			●	●			16.0	11.0	95	10	14	UCR07P 1A1 A095	4
08	●						23.2	14.6	200	-	-	UCP08C 1A1 A200	1
			○	○	●	●	19.9	14.6	200	-	-	UCR08C 1A1 A200	2
			●	●			19.9	14.6	95	12	16	UCR08P 1A1 A095	4
11	●						22.0	17.6	200	-	-	UCP11C 1A1 A200	1
			○	○	●	●	19.2	17.6	200	-	-	UCR11C 1A1 A200	2
			●	●			19.2	17.6	95	16	21	UCR11P 1A1 A095	4
13	●						25.0	20.7	200	-	-	UCP13C 1A1 A200	1
			○	○	●	●	22.5	20.7	200	-	-	UCR13C 1A1 A200	2
			●	●			22.5	20.7	95	18	23	UCR13P 1A1 A095	4
18	●						29.5	28.7	200	-	-	UCP18C 1A1 A200	1
			●	●			25.0	28.7	95	25	29	UCR18P 1A1 A095	4

● Recommended for optimal sealing.

○ Compatible but not recommended for optimal sealing.

All dimensions and images shown are in millimeters and are for reference only.