

# AKB-90WIFI - WiFi Amplifier



## WLAN hi-fi multi-room amplifier

For a wireless music reproduction from your smartphone, tablet PC, stationary PC or Mac. The unit receives the audio signals via the network and transmits them to the connected speakers via the integrated amplifier.

### WLAN hi-fi multi-room amplifier, 2 x 45 W

- WLAN standard 802.11 B/G/N, 2.4 GHz
- System is set up via integrated webserver
- Multi-room function
- Integrated digital hi-fi audio amplifier (class D), suitable for speakers with an impedance of 4-8 Ohm
- Network streaming via DLNA
- Supported audio formats: MP3, WMA, AAC/AAC+, ALAC, FLAC, APE, WAV
- Network protocols: TCP/IP, RDP, HTTP, UPNP
- Gold-plated speaker terminals
- Antenna with SMA antenna connection
- Aluminium housing with mounting flange
- Power supply via supplied PSU

## Technical Data

Channels	:	
Zones	:	
Power rating	:	
Power rating at 2 Ohm	:	
Power rating at 4 Ohm	:	2 x 45 W <sub>RMS</sub> /4 Ohm
Power rating at 8 Ohm	:	
Power rating at 100 V	:	-
Power rating with 4 Ohm bridged operation	:	-
Power rating with 8 Ohm bridged operation	:	-
Peak music power output (P <sub>MAX</sub> )	:	-
Inputs	:	-
Frequency range	:	20-20,000 Hz
Crossover network	:	-
Crossover frequency	:	-
Integrated limiter	:	-
Equalizer bass	:	-
Equalizer midrange	:	-
Equalizer treble	:	-
S/N ratio	:	> 98 dB
Crosstalk attenuation	:	-
THD	:	-
Power supply	:	via suppl. PSU
Mains voltage	:	-
Mains frequency	:	-
Power consumption, operation	:	-
Power consumption, standby	:	-
Standby current	:	-
Alternative operating voltage	:	-
Alternative power supply	:	-
Admiss. ambient temp.	:	-
Dimensions	:	170x34x100 mm
Width	:	170 mm
Height	:	34 mm
Depth	:	100 mm
Rack spaces, RS	:	-

---

Weight : 750 g  
Connections : speaker terminal L/R