

## HD 2AA Metal Light

MPN: EPMHH21E



The toughness & easy-grip convenience of rubber combined with legendary Energizer® performance and dependability for any job site. Shine on...

### Features:

- Custom optics design for exceptional direct & peripheral vision
- Aluminium LED flashlight designed for what consumers want, like LED color aligned with natural daylight
- Smooth digital switching allows options of high, power-saver and emergency strobe modes
- Commercial-grade aluminium alloy gives you confidence for any task
- Aluminium LED flashlight includes 2x AA Energizer® MAX® batteries

FL 1 STANDARD 1000 LUMENS	FL 1 STANDARD 00h	FL 1 STANDARD 000m	FL 1 STANDARD 0m	FL 1 STANDARD
Light Output	Run Time	Beam Distance	Impact Resistant	Water Resistant
300 lumens	4 hours	115 meters	1 meter	IPX4