


## SPE-62HQ - Loudspeaker



### Hi-fi wall and ceiling speaker, 35 W, 8 Ohm

- 2-way version with dome tweeter
- 16 cm (6½") bass speaker with waveguide and 25 mm (1") silk dome
- Excellent sound characteristics
- Stylish flush fit protective metal grille with slim plastic frame
- Protective grille magnetically attached to the speaker front
- For a wall thickness/ceiling thickness from 6 to 35 mm



## Technical Data

Impedance (Z)	: 8 Ohm
Frequency range	: 50-20,000 Hz
Resonant frequency (fs)	: 60 Hz
Music power ( $P_{MAX}$ )	: 70 W
Power rating ( $P_{RMS}$ )	: 35 W
Sensitivity	: 89 dB/W/m
Mounting cutout	: Ø 210 mm
Mounting depth	: 95 mm
Dimensions	: Ø 250 mm x 98 mm
Weight	: 1.6 kg