

TRITON-350 - Amplifier System

500
W_{MAX}

3 Ways



With the TRITON-350,

you will receive a very compact active speaker system with impressive volume reserves which can provide a high-quality sound. The intelligent setup with a 3-channel mixer also allows the application as a stereo subwoofer/satellite system as well as a full range speaker system in mono mode. The satellites can be stacked without cables and be linked to the subwoofer cabinet by means of a smart click system. The supplied stands are adjustable in height and can also be used as spacer tubes on the subwoofer. For transport purposes, the satellites can conveniently be stored in the back of the subwoofer cabinet. **Compact high-performance active PA system, 320 W**

- Subwoofer/satellite system with integrated 3-channel amplifier and 3-channel mixer
- Robust and reinforced plastic cabinet of low resonance
- High-performance bass-reflex subwoofer system with 25 cm (10") bass speaker
- 13 cm (5") midrange speaker which provides a powerful sound and 25 mm (1") CD horn tweeter with titanium cone
- Adjustable volume balance between subwoofer and satellites
- Balanced (comb. XLR) and unbalanced (RCA, jack) inputs and parallel outputs
- Limiter
- Stereo/mono selector switch
- Tone control (effect) for adapting sound to the room acoustics
- Satellites can be stored in the subwoofer cabinet
- Supplied with speaker cables
- Supplied with speaker stands which can also be used as a spacer tube on the subwoofer

djmagazin.de 99

"These small speaker systems can surely provide an impressively powerful performance with a really clear sound. They are unbeatable for general applications with up to 50 people ... and for applications with more, simply connect a second TRITON and link both system via cable. Excellent results."

tastenwelt 02/2016

"An impressive price-performance ratio ... from a compact mono system to a compact power PA system with 2 x TRITON-350 systems, this PA system is suitable for most versatile applications due to its variable design options ... provides a vibrant sound and a rich bass reproduction with an amazing volume level. Thus, it is the right tool for solo entertainers, DJs and smaller bands."

Technical Data

| | |
|-------------------------------|--|
| Power capability | : |
| Max. output power | : 500 W |
| Power rating | : 320 W (SUB), 2 x 50 W (SAT) |
| Speakers | : 1 x 25 cm (10") bass speaker, 2 x 13 cm (5") midrange speaker, 2 x 25 mm (1") horn tweeter |
| Max. rated SPL (system) | : 120 dB 123 dB music 126 dB peak |
| Frequency range | : 50-20,000 Hz |
| Inputs | : |
| Balanced | : comb. XLR jack, 440 mV (line), 7 mV (mic) |
| Unbalanced | : RCA, 3.5 mm jack, 200 mV |
| Outputs | : |
| Line (par. out) | : 6.3 mm jack |
| Satellite speakers (> 150 Hz) | : 2 x 6.3 mm jack |
| S/N ratio | : > 80 dB |
| Power supply | : ~ 230 V/50 Hz/510 VA |
| Admiss. ambient temp. | : 0-40 °C |
| Dimensions | : |
| Subwoofer (WxHxD) | : 350x455x412 mm |
| Satellite speakers (WxHxD) | : 145x230x110 mm |
| Weight | : |
| Subwoofer | : 14 kg |
| Satellite speaker | : 2 kg |
| System | : 18 kg |