

PD10 Specification (10.1" Portable DVD)

Hardware Specification

Laser	:HOP-1200X
Loader	:HT906XG-2
Chip concept (DVD)	:MediaTek MT1389Q +64M SDRAM

Panel Specifications

* Digital Panel	:HSD1010F
* Screen Ratio	:16:9
* Resolution	:1024*600
* Contract Ratio	:400:1
* Brightness	:Average 135cd/m2

Power Supply Specifications

* Power Supply(Adapter)	:DC 9V/1A
* LI Battery	:Built -in 7.4V/(The Battery can play 2 hours)
* Power Indicator (LED)	:Power ON :Green ; Charging :Red ; Low battery power :Red Flashing
* Charge Management	:Fast charge (Power OFF) 2.5-3 Hours :Slow charge 7-9 Hours

Main Features

* Support panel rotating	:Yes
* Card reader	:Yes
* USB	:Yes
* AV Output	:Yes
* Low Power Indicator	:Yes (LED Flashing)
* Playback disc formats	:DVD / DVD+RW/DVD+R/DVD-RW/DVD-R/CD / CD-R / CD-RW
* Support Video format	:MPEG-1(VCD), MPEG-2(SVCD,DVD), MPEG-4, DIVX, XVID, Picture CD
* Support Audio format	:MPEG1, AC3 DECODE, MP3, MP3-PRO, WMA, LC-AAC, HDCD, CD-G
* Support DivX version	:DIVX3.x/DIVX4.x/DIVX5.x/DIVX6 (optional)
* Anti-shock	:No

JACKS

* 4.0 mm DC-IN Jack	:1 pcs
* 3.5 mm stereo earphone jack	:1 pcs
* 3.5 mm AV in	:1 pcs
* 3.5 mm AV out	:1 pcs

Accessories

* Remote control	:1 pcs
* User Manual	:1 pcs
* Warranty cards	:1 pcs
* Earphone	:1 pcs
* Cigar Charger	:1 pcs
* AV Cable	:1 pcs
* AC/DC Adapter	:1 pcs