

# 20" Class Full HD LED Monitor (19.5" Diagonal)

20M38A

 ZOOM



## Key Features

Reader Mode / Flicker Safe | On Screen Control | Colour Weakness Mode

Where to Buy

Add to Compare | PRINT | SHARE 

★★★★★ 0/5

Based on 0 user reviews

# STOCK LIST



Visit Store




Visit Store




Visit Store





## Preset Customized Options with just a Click

OnScreen Control and My Display Presets allow you to easily customize monitor settings with a few clicks of a mouse.




## Customize Your Workspace for Multitasking

Screen Split divides the display for different tasks by resizing the windows on the screen. With PIP Mode you can work while watching a video in a window floating on the screen.

Color Weakness Mode  
**ON**

OFF



## Offers Improved Color Vision to Color Weakness

Color revision algorithms are used to help those with color weakness who have difficulty distinguishing certain ranges of colors can view all the important content.

## General

Size (Inch / cm)	19.5" / 49.4cm
Panel Type	TN
Color Gamut (CIE1976)	72%
Color Depth(Number of Colors)	16.7M colors
Pixel Pitch(mm)	0.271X0.262
Aspect Ratio	16:9
Resolution	1600 x 900
Brightness(Typ.)	200cd/m2
Contrast Ration (DFC)	5M:1
Response Time_Typ.(on/off)	5ms
Viewing Angle(CR≥10)	90/65
Surface Treatment	Anti glare ,3H

---

## Signal Input

D-Sub	Yes
[ Jack Location ]	Back

---

## Power

Input/Output (Type)	Adapter
Input	100-240Vac, 50/60Hz
Consumption( Normal On(EPA))	16W
Normal On(typ.)	20W
Sleep Mode(Max)	0.3W
DC Off(Max)	0.3W

---

## Frequency

D-sub(H-Frequency)	30~83kHz
D-sub(V-Frequency)	56~75Hz

---

## Resolution

PC(D-sub)	1 600 x 900
-----------	-------------

---

## Control Key

Key Number (Power Key Included)	6
Key Type	Tact Type
LED Color(On mode)	White
LED Color(Power save mode)	White Blinking
[ Key Location ]	Bottom

---

## OSD

Language(Country)	English, Germanic, French, Spanish, Italian, Swedish, Finnish, Portuguese, Polish, Russian, Greek, Chinese, Japanese, Korean, Ukrainian, Portuguese(Brazil), Hindi
Number of Language	17

---

## Picture

Picture Mode	Yes
Reader Mode	Yes
Original Ratio	Yes

---

## General Function

DDC/CI	Yes
Intelligent Auto (Auto Adjustment)	Yes
Key Lock	Yes
Plug & Play	Yes

---

## Special Features

Color weakness	Yes
Flicker safe	Yes
Smart Energy saving	Yes
4 screen split	Yes
On Screen Control	Yes

---

## Color

Front	Black Hairline
B/Cover	Black Texture
Stand	Black high glossy
Base	Black Hairline

---

## Stand

Base detachable	Yes
Tilt(Angle)	Yes / -5° ~ 20°

---

## Dimensions - WxDxH (mm)

Set (with Stand)	463.0x167.8x358.8
Set (without Stand)	463.0x57.4x286.5

Box	542x360x118
Wall Mount size (mm)	75 x75

---

## Weight (Kg)

Set (with Stand)	2.2
Set (without Stand)	2
Box	3

---

## Stuffing

Pallet(20ft/40ft/40ft HC)	1080/2376/2640
---------------------------	----------------

---

## Wrap

Packing Material	EPS
Stacking Type	Face Down
Box Printing Type	Flexo
Handle	Hand Hole

---

## Standard

UL (cUL)	Yes
TUV-Type	Yes
FCC-B, CE	Yes
EPA 6.0	Yes
Windows	Yes(win 10)

---

## Accessory



Power Cord

Option

D-Sub

Yes

---

# ECO

[More Compliance Information](#)

---

## WHAT PEOPLE ARE SAYING

[USER REVIEWS](#)

**BE THE FIRST TO WRITE A REVIEW**

[WRITE YOUR OWN REVIEW](#)

---

## QUESTIONS? LET US HELP

Product Support

Simply choose a support option from the icons below:



Email

Send an Email to LG Customer Support to receive a response from an LG support representative.



Phone

Call an LG Support Representative on  
UK : 0344-847-5454  
IE : 01-686-9454  
Monday to Saturday: 9am to 6pm  
Sunday: Closed  
Bank Holidays: Closed



Live Chat

You can chat with LG Support Representative in real time!  
Monday to Saturday: 9am to 5pm  
Sunday: Closed  
Bank Holidays: Closed



## RECENTLY VIEWED



20" Class Full HD LED  
Monitor (19.5"  
Diagonal)

20M38A



