

Model Name	K1	Color Available	Titanium
Weight	11.3g (incl. belt clip)	Dimensions	50mm x 20.5mm x 8mm
Audio Input	Micro USB	Headphone output	Standard 3.5mm Port
Drive ability	16~100 $\Omega$ (recommended)	Sample rate (USB decoding)	Max 96kHz/24bit supported
Battery Capacity	N/A	Power supply	USB on PC
Output Power 1	>75 mW ( 16 $\Omega$ /THD+N < 1%)	Output Power2	>35 mW ( 32 $\Omega$ /THD+N < 1%)
THD+N	< 0.01% (1 kHz)	Output Impedance	$\leq 1 \Omega$
Frequency Response	20 Hz~20 kHz	SNR	$\geq 100$ dB (A-weighted)
Input Sensitivity	>0 dB	MAX input Level	N/A
Crosstalk	$\geq 70$ dB (1 kHz)	Channel imbalance	< 0.3dB
Gain	1.2 dB	Status LED	Yes (blue light when on)
MAX output voltage	3.25 Vp-p	MAX output current	35.93 mA