

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0008560124**
Status: **Active**
Overview: KK® Interconnect System - Molex
Description: KK® Trifurcon™ Crimp Terminal 7258, 22-26 AWG, Bag, Phosphor Bronze Gold (Au)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-001 \(PDF\)](#)
[Product Specification PS-40-02 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
Series 7258
Application Power
Crimp Quality Equipment Yes
Overview KK® Interconnect System - Molex
Packaging Alternative 08-56-0123 (Reel)
Product Name KK®, Trifurcon™
UPC 800754226677

Physical

Gender Female
Material - Metal Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Nickel
Net Weight 0.159/g
Packaging Type Bag
Plating min - Mating 0.762µm
Plating min - Termination 1.270µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.65mm max.
Wire Size AWG 22, 24, 26
Wire Size mm² N/A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Old Part Number 7258-A(P558)L

Reference - Drawing Numbers

Packaging Specification PK-2759-001
Product Specification PS-40-02
Sales Drawing SD-7258



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

7258 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	<u>0011030016</u>
Hand Crimp Tool for Crimp Terminals	<u>0638117400</u>