

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0009508023**
Status: **Active**
Overview: KK® Interconnect System - Molex
Description: KK® 3.96mm Crimp Terminal Housing, Friction Ramp, 2 Circuits

Documents:

3D Model Packaging Specification PK-41695-001 (PDF)
Drawing (PDF) RoHS Certificate of Compliance (PDF)
Product Specification PS-08-50 (PDF)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series 41695
 Application Power, Wire-to-Board
 Comments Glow Wire Equivalent Part Number 41695-2001
 MolexKits Yes
 Overview KK® Interconnect System - Molex
 Product Name KK® 396
 UPC 800755490503

Physical

Breakaway No
 Circuits (maximum) 2
 Color - Resin Natural
 Flammability 94V-0
 Gender Female
 Glow-Wire Compliant No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Material - Resin Polyester
 Net Weight 0.761/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 3.96mm
 Polarized to Mating Part Yes
 Temperature Range - Operating See Product Specification

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Old Part Number 41695-N-D02

Reference - Drawing Numbers

Packaging Specification PK-41695-001
 Product Specification PS-08-50
 Sales Drawing SD-41695



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

41695 Series

Mates With

KK® 396 Header 41791 , 41792 , 41671 ,
41672 , 41661 , 41662

Use With

KK® 396 Crimp Terminals, 2478 , 2578 ,
6838 , 7258 , 45570