

## KEW4105A

### Digital Earth Resistance Tester

#### PRODUCT DATA SHEET

#### KEW4105A

#### DIGITAL EARTH RESISTANCE TESTER

- 20, 200 & 2000  $\Omega$  earth resistance ranges
- Measures earth voltage
- Allows earth resistance testing without tripping earth leakage current breakers
- 2 wire simplified measurement system included as standard
- Dust and drip proof
- Automatic warning of excess tolerance of auxiliary earth spikes
- Complies with BS 7671



#### ACCESSORIES

- ACC7127 2 wire test leads for simplified testing
- ACC7095 1 set of 3 wire test leads (20m, 10m and 5 m leads)
- ACC8032 Auxiliary earth spikes
- Batteries
- Carrying strap
- Carrying case
- Instruction Manual
- Certificate of Conformity

#### OPTIONAL

- Calibration

#### SPECIFICATIONS

Earth Resistance Ranges	20 $\Omega$ , 200 $\Omega$ , 2000 $\Omega$
Earth Voltage Range	200V ac
Withstand Voltage	3700V ac for 1 minutes
Accuracy	$\pm(1\% + 4\text{dgt})$ earth voltage range $\pm(2\% + 1.0 \Omega)$ (20 $\Omega$ range) $\pm(2\% + 3\text{dgt})$ (200 $\Omega$ , 2000 $\Omega$ ranges)
Dimensions	105 x 158 x 70mm
Weight	540g
Power Source	6x 1.5V AA